


92 x 81mm Aperture, Acktar Blackened Laser Beam Block

See More by [Acktar](#)



Acktar Blackened Laser Beam Block



Stock **#13-517** **1 In Stock**

-

1

+

€395^{.00}

ADD TO CART

Volume Pricing	
Qty 1-2	€395,00 each
Qty 3+	€371,90 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Laser Beam Block	Type:
LBD-F-81	Model Number:
Note: Backside has M3 screw holes for 92mm cooling fan attachment (not included)	
Physical & Mechanical Properties	
Black Anodized Aluminum	Construction:
92 x 81mm	Aperture Size:
92 L x 92 W x 10 T	Dimensions (mm):
Optical Properties	
Vacuum Black	Coating:
100 - 10000	Wavelength Range (nm):
Electrical	
20	Maximum Incident Power Density (W/cm²):
50	Maximum Power (W):
Threading & Mounting	
M6 x 1.0	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Coated for High Absorbance of Laser Light
- Tubular Beam Trap or Thin, Flat Beam Block Designs
- M6 Tapped Hole for Easy Post Mounting

Acktar Blackened Laser Beam Traps and Blocks feature proprietary coatings designed to absorb incident laser light from the ultraviolet (UV) to the long-wave infrared (LWIR) spectrums. These Acktar coatings can achieve a reflectivity factor of less than 10⁻⁶ (beam trap designs) and have laser damage thresholds up to 20 W/cm². An M6 tapped hole on both the beam trap and beam block designs allows for easy mounting to optical posts for integration into optical systems. Acktar Blackened Laser Beam Traps and Blocks are available in multiple sizes to accommodate small or large laser beams, increasing overall lab safety by reducing the risk of laser damage. The Flat Beam Block design features back screws for a 92mm cooling fan attachment, allowing for multiple blocks to be coupled to cover large areas.