

9.75" x 13.0", 0.411" FL, Lenticular Array



Stock **#43-026** **7 In Stock**

- 1 + €145^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	€145,00 each
Qty 11-49	€131,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Lens Array

Number of Lenses:
3 per 25.4mm

Physical & Mechanical Properties

Center Thickness CT (inches):
0.09

2.30	Center Thickness CT (mm):
±0.05	Dimensional Tolerance (inches):
9.75 x 13	Dimensions (inches):
247.65 x 330.2	Dimensions (mm):
9 x 12	Effective Size (inches):
±40	Thickness Tolerance (%):
±0.92	Thickness Tolerance (mm):

Optical Properties

10.41	Effective Focal Length EFL (mm):
Acrylic	Substrate: <input type="checkbox"/>
Uncoated	Coating:
400 - 1100	Wavelength Range (nm):
0.41	Effective Focal Length EFL (inches):
1.49	Index of Refraction (n_d):

Environmental & Durability Factors

80 (Maximum)	Operating Temperature (°C):
--------------	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Product Details

- Arrays of Conventional Cylinder Lenses
 - Used as High-Efficiency Diffusers
 - Cylindrical Axis of Lenslet is Aligned Along the First Dimension
- Lenticular Arrays consist of an array of conventional cylindrical lenses which efficiently divide, focus, and diffuse light rays. The focal length of each cylindrical lenslet is typically 3 to 5 times its width and its axis is aligned along the first dimension specified under array dimensions. Lenticular Arrays are ideal for use as high-efficiency diffusers within short working distances, projection screens and stereoscopic (3D) photography.

Technical Information



