

Basler ace2 a2A3840-13gmBAS Monochrome GigE Basic Camera



Basler ace2 GigE Cameras (Front)



Stock **#16-597** ☐ In Stock

[Similar Cameras](#)

-

1

+

€350⁰⁰

ADD TO CART

Qty 1+

€350,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Monochrome Camera

Type:

Basler	Manufacturer:
ace2	Camera Family:
a2A3840-13gmBAS	Model Number:

Physical & Mechanical Properties

55.5 x 29 x 29 (excludes connectors and lens mount)	Dimensions (mm):
<100	Weight (g):
Full	Housing:

Sensor

Not Specified	Image Buffer:
Sony IMX334	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Rolling	Type of Shutter:
1/1.8"	Camera Sensor Format:
8.30	Resolution (MegaPixels):
3,840 x 2,160	Pixels (H x V):
2.00 x 2.00	Pixel Size, H x V (µm):
7.7 x 4.3	Sensing Area, H x V (mm):
13.00	Frame Rate (fps):
8/10/12 bit	Pixel Depth:
Freely Programmable	Exposure Time:
69.2	Dynamic Range (dB):
GigE Vision 2.0, GenICam	Machine Vision Standard:

Electrical

2.9	Power Consumption (W):
-----	------------------------

Hardware & Interface Connectivity

GigE (PoE)	Video Output:
GigE, RJ45 with Screw Locks	Connector:
Power over Ethernet (PoE) or via GPIO with #16-644	Power Supply:
1 opto-coupled input line, 2 general purpose I/O (GPIO) lines	GPIOs:
Hardware Trigger (GPIO), Software Trigger, or Free-Run	Synchronization:
Back Panel	Interface Port Orientation:
6-pin M8	GPIO Connector Type:

Threading & Mounting

1/4-20 with Tripod Mount Adapter #16-641	Mounting Threads:
C-Mbunt	Mount:

Environmental & Durability Factors

-10 to +60	Operating Temperature (°C):
-20 to +80	Storage Temperature (°C):

Regulatory Compliance


Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS


- SONY Pregius S Sensors Available with up to 24MP
- Proven Compact Housing (29 x 29mm)
- Powerful Computer Vision Feature Set with Optional Beyond Features
- [Basler ace GigE Cameras](#) Also Available

Basler ace2 GigE/5GigE Cameras are available in two versions that provide optimized hardware design, proven compact and robust housing, and state of the art CMOS sensor technology with excellent image quality from Sony's 2nd-Gen Pregius, 3rd-Gen STARVIS, or the latest 4th-Gen Pregius S sensors. These second-generation Ace cameras include all of the components of the first-generation Ace cameras along with integrated features such as a status LED, removable IR cut filter, and robust M8 connector. The Basler ace2 GigE/5GigE Camera Basic version offers excellent price to performance ratio with powerful Computer Vision feature set, while the Pro version unlocks unique advanced Beyond features such as Pixel Beyond and Compression Beyond for maximum performance to meet with demanding application requirements. These cameras include the industry proven Basler Pylon SDK Software and Driver and conform to GenICam (GigE Vision 2.0) standards, making them a fast and cost-effective solution to software integration. Basler ace2 Cameras are available in both GigE, 5GigE and USB3.0 interfaces and are ideal for a wide range of applications such as factory automation and industrial robotics.


TECHNICAL INFORMATION




IMX676 Sensor QE Curve




IMX900 Sensor QE Curve




GMAX2505 Sensor QE Curve




IMX546 Sensor QE Curve




IMX545 Sensor QE Curve




GMAX2509 Sensor QE Curve



GMAX2518 Sensor QE Curve



IMX547 Sensor QE Curve



E2525A Sensor QE Curve