

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

Coherent® PowerMax USB PM10-19C Measurement System 1168344 | 10W

See More by [Coherent®](#)



Stock #12-409 [CONTACT US](#)

- 1 + **€1.635,00**

ADD TO CART

Qty 1+

€1.635,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Active Area Diameter (mm):
19

Model Number:
PM10-19C
Coherent Part Number: 1168344

Type:
Meterless

Type of Sensor: Thermopile
Length of Cable (m): 2.5
Computer Interface: USB
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 10600
Long Pulse Joule Mode Range (J): 0.5 - 10
Spectral Compensation Accuracy (%): ±1.5
Maximum Intermittent Power, <5min (W): 30 (air-cooled)
Cooling Method: Water/Air (intermittent)
Maximum Incident Power Density (kW/cm²): 6
Power Range: 10mW - 10W
Maximum Incident Energy Density (J/cm²): 0.6 @ 1064nm, 10ns
Wavelength Range (nm): 190 - 11000
Wavelength Range (µm): 0.19 - 11

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View