


Multi-Grid Standard Stage Micrometer



Stock **#58-607** 4 In Stock

-

1

+

€454^{,23}

ADD TO CART

Volume Pricing	
Qty 1-4	€454,23 each
Qty 5+	€432,39 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

No

NIST Certification:

Physical & Mechanical Properties

Scale Divisions: 0.5mm (25µm divisions), 1.0mm (50µm divisions), 2.0mm (100µm divisions), 4.0mm (200µm divisions), angle grid (15° segments)	
25.4 x 76.2	Dimensions (mm):
Thickness (mm):	
1.50 ±0.100	
Dimensional Tolerance (mm):	
±0.100	
Optical Properties	
Substrate:	
Chrome on Glass	
Surface Quality:	
60-40	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 235:	
Compliant	

PRODUCT DETAILS

- Calibrate Distortion in High Magnification Systems
- The Multi-Grid Stage Micrometer features grids of varying frequency, and is ideal for calibrating distortion in microscopic systems. Grid sizes are 0.5mm (25µm divisions), 1.0mm (50µm divisions), 2.0mm (100µm divisions) and 4.0mm (200µm divisions). Micrometer also features an angle grid (15° segments). Target is chrome on glass, 1" x 3" x 1.5mm.