

a-BBO Wollaston Polarizer



Stock #68-823 **6 In Stock**

- 1 + €1.255⁰⁰

ADD TO CART

Volume Pricing

Qty 1+ €1.255,00 each

Need More? [Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

10.0 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**


18.00 **Length (mm):**

+0.0/-0.2	Dimensional Tolerance (mm):
Crystalline Wollaston Polarizer	Construction:
±0.1	Length Tolerance (mm):
Black Anodized Aluminum	Housing:
Optical Properties	
200,000:1	Extinction Ratio:
α-BBO	Substrate: <input type="checkbox"/>
20-10	Surface Quality:
M4 @ 632.8nm	Transmitted Wavefront, P-V:
<3	Beam Deviation (arcmin):
15 - 27 16 @ 800nm	Beam Separation (°):
220 - 3500	Wavelength Range (nm):
10 J/cm ² @ 1064nm, 20ns	Damage Threshold, By Design: <input type="checkbox"/>
15 - 27 (16 @ 800nm)	Separation Angle (°):
Regulatory Compliance	
View	Certificate of Conformance:


Product Details

- Multiple Polarization Materials Available
- UV to IR Ranges Offered
- Large Deviation of Ordinary and Extraordinary Rays
- [Rochon Polarizers](#) Also Available

Wollaston Polarizers consist of two birefringent right angle prisms cemented together, such that their optical axes are perpendicular. As light passes through the polarizer, a symmetric deviation between the ordinary and extraordinary beams is created. The resulting beams are of orthogonal linear polarization states and have equal intensity and a large angular deviation. Users have access to both the ordinary and extraordinary rays, making them ideal for laboratory experiments.



Technical Information



Stock No.	Outer Diameter	Clear Aperture	Length	Separation Angle α (°)
#68-820	25.4mm	10.0mm	28.0mm	2 - 3 (2 @ 1064nm)
#68-821	25.4mm	10.0mm	18.0mm	16.7 - 22.5 (19 @ 980nm)
#68-822	25.4mm	10.0mm	18.0mm	19.6 - 23.3 (20 @ 1550nm)
#68-823	25.4mm	10.0mm	18.0mm	15 - 27 (16 @ 800nm)

