

[See all 26 Products in Family](#)

TECHSPEC®

9mm Dia. x -12mm FL, VIS 0°, Inked, Double-Concave Lens



Stock **#48-939-INK**

CONTACT US

☐ [Other Coating Options](#)

-

1

+

€55<sup>.50</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | €55,50 each                   |
| Qty 10-25      | €49,75 each                   |
| Qty 26-49      | €44,25 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Double-Concave Lens

Type:

Physical & Mechanical Properties

|                                      |                                                   |
|--------------------------------------|---------------------------------------------------|
| 9.00 ±0.025                          | Diameter (mm):                                    |
| Protective as needed                 | Bevel:                                            |
| 1.50                                 | Center Thickness CT (mm):                         |
| ±0.05                                | Center Thickness Tolerance (mm):                  |
| <1                                   | Centering (arcmin):                               |
| 8.1                                  | Clear Aperture CA (mm):                           |
| 2.43                                 | Edge Thickness ET (mm):                           |
| Optical Properties                   |                                                   |
| -12.00                               | Effective Focal Length EFL (mm):                  |
| N-SF11                               | Substrate: <input type="text"/>                   |
| 1.33                                 | f/#:                                              |
| 0.38                                 | Numerical Aperture NA:                            |
| VIS 0° (425-675nm)                   | Coating:                                          |
| 425 - 675                            | Wavelength Range (nm):                            |
| -12.41                               | Back Focal Length BFL (mm):                       |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm | Coating Specification:                            |
| 587.6                                | Focal Length Specification Wavelength (nm):       |
| ±1                                   | Focal Length Tolerance (%):                       |
| -19.16                               | Radius R <sub>1</sub> =R <sub>2</sub> (mm):       |
| 40-20                                | Surface Quality:                                  |
| 5 J/cm² @ 532nm, 10ns                | Damage Threshold, By Design: <input type="text"/> |
| 1.5λ                                 | Power (P-V) @ 632.8nm:                            |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:                     |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| View                  | Certificate of Conformance: |


## Product Details

- AR Coated to Provide <0.4% Reflectance per Surface for 425 - 675nm
- Designed for 0° Angle of Incidence
- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#)

TECHSPEC® VIS 0° Coated Double-Concave (DCV) Lenses are designed to have two inward curved surfaces and a negative focal length similar to Plano-Concave (PCV) lenses. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Double-Concave (DCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes

TECHSPEC® VIS 0° Coated Double-Concave (DCV) Lenses are best used in 0° angle of incidence situations and provide optimized transmission in the 425nm – 675nm range. These lenses are also available [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS-NIR](#), [NIR I](#), or with [NIR II](#) AR coating options.

## Technical Information



## Coating Curves

### Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts