


Laser Safety Window LS24 YAGW 304.8 x 304.8mm



Laser Safety Windows

Stock **#75-521** NEW CONTACT US

-

1

+

€179⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€179,00 each
Qty 6-10	€161,10 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

EN 207/208 Ratings:

- D AB8 + IRMAB3 180-315

D AB5 + I AB8 + RMAB7 316-428

D AB5 + IRMAB6 429-441

DIRMAB1 669-713

DIRMAB3 740-1115
DIRMAB4 761-1102
DIRMAB5 779-1050
D AB5 + IRMAB7 811-1050

Polymer

Filter Material:

LS24

Filter:

Physical & Mechanical Properties

304.8 x 304.8

Dimensions (mm):

3.00

Thickness (mm):

Optical Properties

>7 @ 200-400
>7 @ 850-1100
>5 @ 9000-10600

Optical Density OD (Average):

Green

Color:

50

Visible Light Transmission VLT (%):

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- CE Certified Laser Radiation Protection
- Available for UV, VIS, and NIR Wavelengths
- 200mm x 100mm Size Ideal for Small Enclosures
- 304.8mm x 304.8mm Sizes Also Available

Laser Safety Windows feature high optical density in a specified wavelength range across the UV, VIS, and NIR spectra. Made from acrylic and polycarbonate, these laser safety windows are CE certified to protect against laser radiation. These windows are available in 200 x 100mm for easy integration into small equipment doors, windows, and enclosures. 304.8 x 304.8mm sizes are also available. Laser Safety Windows are ideal for blocking laser radiation while providing safe viewing of laser environments in materials processing, manufacturing, and laboratory applications featuring Nd:YAG, CO₂, fiber, and other laser sources.

Warning: Because of the potential for eye damage, the degree of protection required in each circumstance should be determined by the Laser Safety Officer, the industrial hygienist, or the individual responsible for the safety program.