

Power Supply for 5-7mW HeNe Laser, 24 VDC, Bare Wire Leads



DC with Bare Leads HeNe Laser Power Supply

Stock **#18-966** [CONTACT US](#)

- 1 + €340⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€340,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads



SPECIFICATIONS

General

Type:

OEM

Compatible Laser Models:

[1125](#), [1125P](#), [1137](#), [1137P](#)

L28 Series	Model Number:
	Compatible Laser Stock Number: #62-722, #62-723, #62-724, #62-725
Physical & Mechanical Properties	
4.25 x 3.30 x 1.20	Dimensions (inches):
Electrical	
2.5-25	Output Power (W):
2.32 (Max. Current Draw)	Input Current (A):
Hardware & Interface Connectivity	
2300	Output Voltage (V):
6	Output Current (mA):
High Voltage Alden Connector	Connector:
20-30 DC	Input Voltage (V):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

TECHNICAL INFORMATION

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

