

a-BBO Rochon Polarizer



Stock #68-827 **20+ In Stock**

- 1 + €1.275⁰⁰

ADD TO CART

Volume Pricing

Qty 1+ €1.275,00 each

Need More? [Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

10.0 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

18.00 **Length (mm):**

Dimensional Tolerance (mm):	
+0.0/-0.2	
Construction:	
Crystalline Rochon Polarizer	
Length Tolerance (mm):	
±0.1	
Housing:	
Black Anodized Aluminum	
Optical Properties	
Extinction Ratio:	
200,000:1	
Substrate: <input type="checkbox"/>	
α-BBO	
Surface Quality:	
20-10	
Transmitted Wavefront, P-V:	
λ/4 @ 632.8nm	
Beam Deviation (arcmin):	
<3	
Wavelength Range (nm):	
200 - 3500	
Damage Threshold, By Design: <input type="checkbox"/>	
10 J/cm ² @ 1064nm, 20ns	
Separation Angle (°):	
8.0 - 14 (8 @ 800nm)	

Regulatory Compliance	
Certificate of Conformance:	
View	


Product Details

- Multiple Polarization Materials Available
- Ordinary Rays Pass Through Undeviated
- Extraordinary Rays Deviate
- [Wollaston Polarizers](#) Also Available

Rochon Polarizers consist of two birefringent material prisms in optical contact with one another. The ordinary and extraordinary rays remain collinear through the first prism. Upon entering the second prism, the ordinary rays do not experience a change in the refractive index and pass through the prism without deviation, while the extraordinary rays refract at the interface.



Technical Information



Stock No.	Outer Diameter	Clear Aperture	Length
#68-824	25.4mm	10.0mm	28.0mm
#68-825	25.4mm	10.0mm	28.0mm
#68-826	25.4mm	10.0mm	16.0mm
#68-827	25.4mm	10.0mm	18.0mm

