

[See all 21 Products in Family](#)

BFLY-PGE-13E4C-CS 1/1.8" Blackfly® PoE GigE Color Camera

See More by [Teledyne FLIR](#)



Teledyne FLIR IIS Blackfly® GigE Cameras (Front)



Stock #88-044 **1 In Stock**

⊖ 1 ⊕ €486⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€486,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

BFLY-PGE-13E4C-CS	Model Number:
FLIR	Manufacturer:
Blackfly®	Camera Series:

Physical & Mechanical Properties

29 x 29 x 30 (excludes connectors and lens mount)	Dimensions (mm):
90	Weight (g):
Full	Housing:

Sensor

16MB	Image Buffer:
1/1.8"	Sensor Format:
1.30	Resolution (Megapixels):
60.00	Frame Rate (fps):
1,280 x 1,024	Pixels (H x V):
5.3 x 5.3	Pixel Size, H x V (µm):
6.78 x 5.43	Sensing Area, H x V (mm):
e2v EV76C560	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
10 bit	Pixel Depth:
15µs - 1s	Exposure Time:
50.82 (Mode 0) 59.48 (Mode 7)	Dynamic Range (dB):
GigE Vision v1.2	Machine Vision Standard:

Electrical

2	Power Consumption (W):
---	-------------------------------

Hardware & Interface Connectivity

GigE (PoE)	Interface:
GigE, RJ45 with Screw Locks	Connector:
Power Supply Required and Sold Separately. USA: #88-063 Europe: #88-063 Japan: #88-063 Korea: Not Available China: #88-063	Power Supply:
1 opto-isolated input, 1 opto-isolated output	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
6-pin Hirose (HR10)	GPIO Connector Type:

Threading & Mounting

CS-Mount	Mount:
¼-20 with Tripod Mount Adapter #88-210	Mounting Threads:

Environmental & Durability Factors

0 to +45 **Operating Temperature (°C):**

-30 to +60 **Storage Temperature (°C):**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 240:**

Product Details

Two GigE cables are required if using the PoE injector. Use ([#03-618](#)) 5mm Spacer to convert CS-Mount Cameras to C-Mount. Software available for [download](#).

- Ultra-Compact Design
- Power over Ethernet (PoE) for Maximum Flexibility
- Includes Image Capture Software and FlyCapture2 SDK
- [USB3](#) Versions Also Available



Teledyne
Authorized
Distributor

Teledyne FLIR IIS Blackfly®: Legacy series Machine Vision Cameras that fit anywhere

The Blackfly® camera line combines Sony, Aptina, and e2v sensors with a host of unique features.

The **Blackfly®** machine vision camera line combines the high throughput of USB 3.0 or GigE, offering a number of highly sensitive sensors. The camera combines a comprehensive list of unique features, offering industry-leading capabilities, affordability, and uncompromising value. The ultra-compact Blackfly camera measures 29 x 29 x 30mm, weighs just 36 grams, uses 3 watts of power, and includes a 3-year warranty.

The **Blackfly®** is available with either color or monochrome sensors, providing a versatile imaging solution to easily obtain the exact images required to accelerate application development. A range of camera accessories and a common form factor provide a consistent platform for integration across the range of available sensor formats, resolution, and frame rates.

Note: Two GigE cables are required if using the PoE injector. Use ([#03-618](#)) 5mm Spacer to convert CS-Mount Cameras to C-Mount. Software available for [download](#).

Blackfly® GigE color / monochrome

- Models are available with various image sensors in a range of resolutions: 1.2 MP, 1.3 MP, 2.0 MP, 2.3 MP, 3.2 MP, and 5.0 MP

Features

- Perfect analog camera replacement
- Data interface options: either GigE or [USB3](#)
- CS-mount
- Ultra-compact form factor, measuring 29 x 29 x 30mm, weighs only 36g
- On-camera image processing includes color interpolation, gamma, and LUT
- 16 MByte frame buffer
- LED status indicator
- Supports partial readout via ROI, binning, decimation
- Triggering modes include standard, bulb, overlapped, multi-shot (not all sensors support all modes)
- 2 user configuration sets for custom camera settings
- Bit depth: 10 or 12-bit
- Advanced auto-algorithms or precise manual control over image capture and on-camera pre-processing
- Windows or Linux platforms (32 or 64-bit)
- Camera control via FlyCapture SDK or 3rd-party USB3 Vision software

Applications

- Life science instrumentation
- Factory automation
- Biometrics kiosk solutions
- Ophthalmoscopy
- 3D scanning
- Automated optical inspection
- Food & Beverage industry