

[See all 20 Products in Family](#)

BFLY-PGE-50S5M-C 2/3" Blackfly® PoE GigE Monochrome Camera

See More by [Teledyne FLIR](#)



Teledyne FLIR IIS Blackfly® GigE Cameras (Front)



Stock **#34-513** **2 In Stock**

[Similar Cameras](#)

-

1

+

€920⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€920,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Monochrome

Spectrum:

General

Type:

Monochrome Camera	
BFLY-PGE-50S5M-C	Model Number:
FLIR	Manufacturer:
Blackfly®	Camera Series:

Physical & Mechanical Properties

29 x 29 x 30 (excludes connectors and lens mount)	Dimensions (mm):
36	Weight (g):
Full	Housing:

Sensor

16MB	Image Buffer:
2/3"	Sensor Format:
5.00	Resolution (Megapixels):
22.00	Frame Rate (fps):
2,448 x 2,048	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
8.45 x 7.07	Sensing Area, H x V (mm):
Sony IMX264	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
22µs - 11.99s	Exposure Time:
70.78	Dynamic Range (dB):
GigE Vision v1.2	Machine Vision Standard:

Electrical

2.5	Power Consumption (W):
-----	------------------------

Hardware & Interface Connectivity

GigE (PoE)	Interface:
GigE, RJ45 with Screw Locks	Connector:
Power Supply Required and Sold Separately. USA: #88-063 Europe: #88-063 Japan: #88-063 Korea: Not Available China: #88-063	Power Supply:
1 opto-isolated input, 1 opto-isolated output	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
6-pin Hirose (HR10)	GPIO Connector Type:

Threading & Mounting

C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #88-210	Mounting Threads:

Environmental & Durability Factors

0 to +45	Operating Temperature (°C):
-30 to +60	Storage Temperature (°C):

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 240:

Product Details

- Ultra-Compact Design
- Power over Ethernet (PoE) for Maximum Flexibility
- Includes Image Capture Software and FlyCapture2 SDK
- [USB3](#) Versions Also Available



Teledyne FLIR IIS Blackfly®: Legacy series Machine Vision Cameras that fit anywhere

The Blackfly® camera line combines Sony, Aptina, and e2v sensors with a host of unique features.

The **Blackfly®** machine vision camera line combines the high throughput of USB 3.0 or GigE, offering a number of highly sensitive sensors. The camera combines a comprehensive list of unique features, offering industry-leading capabilities, affordability, and uncompromising value. The ultra-compact Blackfly camera measures 29 x29 x30mm, weighs just 36 grams, uses 3 watts of power, and includes a 3-year warranty.

The **Blackfly®** is available with either color or monochrome sensors, providing a versatile imaging solution to easily obtain the exact images required to accelerate application development. A range of camera accessories and a common form factor provide a consistent platform for integration across the range of available sensor formats, resolution, and frame rates.

Note: Two GigE cables are required if using the PoE injector. Use (#03-618) 5mm Spacer to convert CS-Mount Cameras to C-Mount. Software available for download.

Blackfly® GigE color / monochrome

- Models are available with various image sensors in a range of resolutions: 1.2 MP, 1.3 MP, 2.0 MP, 2.3 MP, 3.2 MP, and 5.0 MP

Features

- Perfect analog camera replacement
- Data interface options: either GigE or [USB3](#)
- CS-mount
- Ultra-compact form factor, measuring 29 x29 x30mm, weighs only 36g
- On-camera image processing includes color interpolation, gamma, and LUT
- 16 MByte frame buffer
- LED status indicator
- Supports partial readout via ROI, binning, decimation
- Triggering modes include standard, bulb, overlapped, multi-shot (not all sensors support all modes)
- 2 user configuration sets for custom camera settings
- Bit depth: 10 or 12-bit
- Advanced auto-algorithms or precise manual control over image capture and on-camera pre-processing
- Windows or Linux platforms (32 or 64-bit)
- Camera control via FlyCapture SDK or 3rd-party USB3 Vision software

Applications

- Life science instrumentation
- Factory automation
- Biometrics kiosk solutions
- Ophthalmoscopy
- 3D scanning
- Automated optical inspection
- Food & Beverage industry