

[See all 127 Products in Family](#)

Allied Vision Alvium 1800 U-234c, 1/1.2" 5.1 CS-Mount, Right Angle USB 3.1 Color Camera

See More by [Allied Vision](#)



[+2](#)

Stock **#26-357** **1 In Stock**

-

1

+

€590^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€590,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads	
Color	Spectrum:
General	
Color Camera	Type:
Alvium 1800 U-234c	Model Number:

Allied Vision	Manufacturer:
Avium Right Angle	Camera Series:
Physical & Mechanical Properties	
29 x 29 x 33 (includes connectors and lens mount)	Dimensions (mm):
65	Weight (g):
Full	Housing:
Sensor	
256KB	Image Buffer:
1/1.2"	Sensor Format:
2.40	Resolution (Megapixels):
40.00	Frame Rate (fps):
1,936 x 1,216	Pixels (H x V):
5.86 x 5.86	Pixel Size, H x V (µm):
11.3 × 7.1	Sensing Area, H x V (mm):
Sony IMX249	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
53 µs - 10s	Exposure Time:
+5 to +65	Dynamic Range (dB):
USB3 Vision v1.0, GenICam	Machine Vision Standard:
Electrical	
2.1	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.1 Gen 1	Interface:
USB 3.1 Gen 1, Micro-B	Connector:
Power over USB or via GPIO	Power Supply:
4 Programmable TTL GPIOs	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
USB3 Vision v1.0, GenICam	GPIO Connector Type:
Threading & Mounting	
CS-Mount	Mount:
1/4-20 and M6 with Tripod Mount Adapter #14-156	Mounting Threads:
Environmental & Durability Factors	
-20 to +85	Operating Temperature (°C):
7-pin JST	Storage Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Right Angle USB Port Orientation
- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALVUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- [Allied Vision Alvium USB 3.1 Cameras](#) Also Available

Allied Vision Alvium Right Angle USB 3.1 Cameras feature ALVUM® System on Chip (SoC) technology and a right-angle USB port in a lightweight compact form factor, offering a comprehensive image processing library for advanced onboard image correction, preprocessing functions to relieve host computer and processor workload, and allow for easy system integration. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Alvium Right Angle USB 3.1 Cameras feature a 90° right angle USB port and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

Note: Board level versions do not have a lens mount.