

[See all 145 Products in Family](#)

Allied Vision Alvium 1800 U-811c, 2/3" 8.1MP C-Mount, USB 3.0 Color Camera

See More by [Allied Vision](#)



Allied Vision Alvium USB 3.1 Cameras



Stock **#19-587** **8 In Stock**

[Similar Cameras](#)

- 1 + €910.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€910,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Color

Spectrum:

General

Color Camera

Type:

1800 U-811c	Model Number:
Allied Vision	Manufacturer:
Avium	Camera Series:

Physical & Mechanical Properties

38 x 29 x 29 (includes connectors and lens mount)	Dimensions (mm):
65	Weight (g):
Full	Housing:

Sensor

256KB	Image Buffer:
2/3"	Sensor Format:
8.10	Resolution (Megapixels):
43.00	Frame Rate (fps):
2,848 x 2,848	Pixels (H x V):
2.74 x 2.74	Pixel Size, H x V (µm):
7.8 x 7.8	Sensing Area, H x V (mm):
Sony IMX546	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10/12 Bit	Pixel Depth:
168µs - 10s @ 450 MBps 160µs - 10s @ 200 MBps	Exposure Time:
USB3 Vision v1.0, GenICam	Machine Vision Standard:

Electrical

3.3	Power Consumption (W):
-----	-------------------------------

Hardware & Interface Connectivity

USB 3.0 Gen 1	Interface:
USB 3.0 Gen 1, Micro-B	Connector:
Power over USB or via GPIO	Power Supply:
4 Programmable TTL GPIOs	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
7-pin JST	GPIO Connector Type:

Threading & Mounting

C-Mount	Mount:
1/4-20 and M6 with Tripod Mount Adapter #14-156	Mounting Threads:

Environmental & Durability Factors

-20 to +65 (housing temperature)	Operating Temperature (°C):
-20 to +85	Storage Temperature (°C):

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 240:

Product Details

- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALVIUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- Up to 24.60 MegaPixels, 1.2" Sensor Format
- [Allied Vision Alvium Right Angle USB 3.1 Cameras](#) Also Available

Allied Vision Alvium USB 3.0 Cameras feature a lightweight compact form factor with ALVIUM® System on Chip (SoC) technology, offering a comprehensive image processing library for advanced onboard image correction and preprocessing functions to relieve host computer and processor workload. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Alvium USB 3.0 Cameras feature a USB port on the back panel and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

Note: Board level versions do not have a lens mount.