

Allied Vision Prosilica GT2050 1" NIR CMOS Camera

See More by [Allied Vision](#)



Stock **#88-476** [CONTACT US](#)

[Similar Cameras](#)

- 1 + **€3.078,00**

ADD TO CART

Qty 1+

€3.078,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
NIR Camera

Manufacturer:
Allied Vision

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#87-412](#)

Image Buffer: 128MB
Camera Family: Prosilica GT
Model Number: GT 2050 NIR
Imaging Sensor: CMOSIS CIM4000
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1"
Resolution (MegaPixels): 4.20
Pixels (H x V): 2,048 x 2,048
Pixel Size, H x V (µm): 5.5 x 5.5
Sensing Area, H x V (mm): 11.6 x 11.6
Frame Rate (fps): 28.70
Pixel Depth: 8/12 bit
Exposure Time: 1µs - 126s
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately. USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281
Power Consumption (W): 3.5 (12VDC External Power Supply) 4.3 (PoE)
GPIOs: 1 opto-isolated input, 2 opto-isolated outputs, 1 non-isolated input, 2 non-isolated outputs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 70.5 x 53.3 x 33 (excludes connectors and lens mount)
Weight (g): 210
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 56.7
Operating Temperature (°C): -20 to +65
Storage Temperature (°C): -20 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: GigE Vision V1.2, GenICam SFNC V1.2.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant