

Educational Spectroscope



Stock #72-411 [CONTACT US](#)

- 1 + €725^{.00}

[ADD TO CART](#)

Volume Pricing

Qty 1-4	€725,00 each
Qty 5-9	€652,50 each
Qty 10+	€543,75 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties

7.00 **Weight (lbs):**

16 x 10 x 9 **Dimensions (inches):**

Optical Properties

50 Angstroms (5nm) **Resolution:**

3600 - 7600 Angstroms

Wavelength:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Measure Wavelengths of Various Light Sources
- Detect Elements by Flame Emission
- Ideal for Educational Classroom Use

Spectroscope is a replica diffraction grating instrument with a scale to show approximate wavelengths in Angstrom units. Housing is a single-piece aluminum casting mounted on a nickel-plated steel post supported by a cast iron tripod base. In use, the white face reflector is positioned to give a small amount of back lighting to a photographic film scale, so that it may be clearly seen against the superimposed image of the spectrum. To observe solar spectrum, use a cloud and the adjustable slit. Will detect Ca, Pa, Sr, Li, K, Na, Rb, Cu, etc. by flame emission. As slit is closed, prominent Fraunhofer lines appear. In lab, source is placed in front of slit and light from lamp directed in scale. 16" x 10" x 9"; 7 lbs.
