

EO Deluxe Power Meter



Deluxe Power Meter #89-305

Stock **#89-305** 1 In Stock

-

1

+

€1.395⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€1.395,00 each
Qty 5+	€1.250,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Operating Lifetime (hours):

670 (with 4 x AA Alkaline Batteries)

Type:

Average Power

Type of Display:

76 x 57mm Non-Touch Screen LCD, 32mm Digit Height

Note:

EO Deluxe Power Meter	
None	Stats:
W and dBm	Units:
Physical & Mechanical Properties	
210 x 122 x 44	Dimensions (mm):
470	Weight (g):
±1	Accuracy (%):
Sensor	
Sold Separately	Type of Sensor:
Hardware & Interface Connectivity	
None	Computer Interface:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Product Details

- Premier Laser Power and Energy Meter Features Touch Screen Display
- Deluxe Laser Power Meter Features Digital Display
- USB Laser Power Meter Features Direct Interface to Computer
- [Edmund Optics Power and Energy Detectors](#) Sold Separately

Edmund Optics® Laser Power and Energy Meters are offered in a range of models to meet different user requirements. The Premier Laser Power and Energy Meter reads all EO power and energy detectors and features a 640 x 480 resolution, 5.6" diagonal, color touch screen display. The Premier provides multiple real-time statistical functions such as standard deviation, RMS and PTP stability, and pulse number and repetition rate, along with the ability to save data directly to a USB key. The Deluxe Laser Power Meter is designed for use with thermopiles and optical detectors. The Deluxe's ergonomic and low power design can last 670 hours on just four AA batteries, features a large 76 x 57mm display, and provides single-button access to all functions. The USB Laser Power Meter is also for use with thermopile and optical detectors and can be connected directly to a PC using the including software and the port powered-USB interface.

Note: Manuals are available for download for all models.