

[See all 11 Products in Family](#)

**TECHSPEC® f/2.5, Visible, 8.0mm HEO Series M12 Lens**



8.0mm Focal Length

Stock #63-759 **11 In Stock**

⊖ 1 ⊕ €159<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-49	€159,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

HEO Series **Product Family:**

M12 Imaging Lens **Type:**

No **IR Cut Filter:**

Meets IEC IPX7 and IPX9K **Imaging Lens Type:**

## Physical & Mechanical Properties

Fixed	<b>Iris Option:</b>
15.00	<b>Length (mm):</b>
14	<b>Maximum Diameter (mm):</b>
14	<b>Outer Diameter (mm):</b>
4	<b>Weight (g):</b>

## Optical Properties

**Horizontal Field of View @ Max Sensor Format:**  
390.7mm - 51.9°

**Field of View at Max Sensor Format:**  
Horizontal: 390.7mm - 51.9°  
Vertical: 249.7mm - 34.5°  
Diagonal: 442.8mm - 57.8°

**Horizontal Field of View, 1/1.7" Sensor:**  
390.7mm - 51.9°

**Horizontal Field of View, 1/2" Sensor:**  
341.7mm - 46.1°

**Horizontal Field of View, 1/2.5" Sensor:**  
306.3mm - 41.8°

**Horizontal Field of View, 1/3" Sensor:**  
249.6mm - 34.5°

**Horizontal Field of View, 1/4" Sensor:**  
184.6mm - 25.9°

**Maximum Image Circle (mm):**  
10.00

**Numerical Aperture NA, Object Side:**  
0.0039

**Resolution, On-Axis:**  
145 lp/mm @ 20% Contrast

**Number of Elements (Groups):**  
6 (5)

**Wavelength Range (nm):**  
425 - 675

**Focal Length FL (mm):**  
8.00

**Working Distance (mm):**  
400 - ∞

**Aperture (f/#):**  
f/2.5

**Distortion (%):**  
-9.15 @ Full Field

**Back Focal Length BFL (mm):**  
8.67 - 8.53

**Coating Specification:**  
425 - 625nm BBAR

**Entrance Pupil Position (mm):**  
3.67

**Object Space Principal Plane (mm):**  
7.82

**Image Space Principal Plane (mm):**  
0.97

**Maximum Distortion (%):**  
-9.15

**Exit Pupil Position (mm):**  
-7.65

**Lens Wavelength Range:**  
VIS

## Sensor

**Maximum Sensor Format:**  
1/1.7"

**Pixel Size (µm):**  
5.00

## Threading & Mounting

**Filter Thread:**  
N/A

**Mount:**

## Environmental & Durability Factors

IPX7 and IPX9K	<b>Environmental Rating:</b>
Waterproof (IPX7 and IPX9K)	<b>Type of Ruggedization:</b>

## Regulatory Compliance

<b>Compliant</b>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<b>Compliant</b>	<b>REACH 241:</b>

## Product Details

- Up to 1/2", S-Mount Lens
- Up to 1.2 MegaPixels, 5µm Pixel Size Sensors
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- 2.2mm to 8mm Focal Length


TECHSPEC® HEO Series M12 Lenses integrate high performance optics into a sealed, ruggedized enclosure. Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high-pressure, high-temperature water spray downs. Threaded for M12 x0.5, these lenses are optimized for 1/3" and 1/2" sensor formats. Each HEO Series Lens is waterproof, dustproof, and fog proof with the ability to be hermetically sealed to a camera. TECHSPEC® HEO Series M12 Lenses are ideal for harsh environment applications, such as automotive. Prescription data is available by submitting a [Request for Prescription Form](#)

**Note:** Compatible [TECHSPEC® M12 Imaging Lens Accessories](#) available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- **Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- **Rugged Blue Series M12 Lenses:** Stabilized ruggedization versions of our Blue Series M12 Lenses, utilizing the same optics.
- **Green Series M12 Lenses:** Finite conjugate designs optimized for machine vision working distances.
- **Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- **HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- **Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.


## Technical Information




#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Distortion Plot




#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Relative Illumination Plot




#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Working Distance versus Field of View Plot




#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Modulated Transfer Function (MTF) Plot, 400mm Working Distance, f2.5



#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Depth of Field Plot, 400mm Working Distance, f2.5



#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Modulated Transfer Function (MTF) Plot, 8000mm Working Distance, f2.5



#63-759, f/2.5, Visible, 8.0mm HEO Series M12 Lens, Depth of Field Plot, 8000mm Working Distance, f2.5

Focal Length	A	B	C	D
2.2mm	21.0mm	16.4mm	2.2mm	5.4mm
3.6mm	14.0mm	14.1mm	4.5mm	4.5mm
8.0mm	14.0mm	15.0mm	8.7mm	4.0mm

