


Film-Format Achromatic Polymer Retarder $\lambda/4$ 25.4mm Dia Uncoated



Stock **#70-709** 3 In Stock

-

1

+

€675^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	€675,00 each
Qty 11-25	€510,00 each
Qty 26+	€473,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Note:
Slow axis marked with blue dot on part and stripe on protective film

Physical & Mechanical Properties

Diameter (mm):
25.40 +/- 0.15

Thickness (mm):

0.55 Nominal	
Optical Properties	
±10	Angle of Incidence (°):
Polymer Stack	Substrate: ☐
λ/4 ± λ/100	Retardance:
60-40	Surface Quality:
700 - 1550	Wavelength Range (nm):
Damage Threshold, By Design: ☐ 500 Watt/cm² CW, .3 J/cm² 10 nsec pulses @ 532nm, 2 J/cm² 20 nsec pulses @ 1064nm typical	
Uncoated	Coating Type:

Environmental & Durability Factors	
-20 to +40	Operating Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Ultra-Thin ≤0.55mm Substrates for OEM Integration
- Options For 600-1100nm and 700-1550nm
- Wide Acceptance Angle Tolerance of ±10°

Ultra-Thin NIR Achromatic Polymer Retarders feature an optically fused and adhesive-free construction, allowing for high temperature resistance, high transmission, and an ultra-thin format. These retarders are designed with a multi-layer polymer stack and feature a 0.35mm thickness for λ/2 retarders and 0.55mm thickness for λ/4 retarders. Available either uncoated or with an AR-Coating, these retarders offer a retardance tolerance of λ/100 in the NIR range at a wide range of angles of incidence. Uncoated Ultra-Thin NIR Achromatic Polymer Retarders offer an increased retardance range of 700-1550nm while the coated options feature improved transmission from 700-1100nm. These waveplates are ideal for NIR imaging and analytical instrumentation, as well as OEM integration and other applications requiring a small form factor.