

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® Broadband VIS TX - 3X Research-Grade Variable Beam Expander



Research-Grade Variable Beam Expanders



Stock #87-563 3-4 DAYS

- 1 +

€1.300,00

ADD TO CART

Qty 1-4

€1.300,00

Qty 5+

€1.148,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0 ±0.06

Coating:

BBAR (425-700nm)
Design Wavelength DWL (nm): Broadband
Entrance Aperture (mm): 10
Exit Aperture (mm): 30
Expansion Power: 1X - 3X
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 171.10
Mounting Threads: Input: Male C-Thread (1" x 32 TPI) Output: Male T-Thread (M42 x 0.75)
Transmission (%): >95 @ DWL
Type: Beam Expander
Weight (g): 556
Housing Diameter (mm): 58.2
Transmitted Wavefront, P-V: <λ/4 @ 633nm for Input Beam ≤5mm
Coating Specification: R _{avg} <1.0% @ 425 - 700 nm
Wavelength Range (nm): 425 - 700
Style: Variable Magnification
Damage Threshold, By Design: ☐ 5 J/cm ² @ 633nm, 10ns, 20Hz
Divergence Adjustment: Non-Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View