

FLIR E5 Pro Thermal Imaging Camera



Stock **#75-073** NEW **3 In Stock**

-

1

+

€1.349^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€1.349,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Standard Measurement Temperature (°C):
-20°C to 400°C (-4°F to 752°F) in two ranges

Thermal

Spectrum:

General

ExSeries

Model Number:

Contents of Kit:
Infrared camera (with LED flashlight), hard transport case, battery (inside camera), power supply (with EU, UK, US and AU plugs), FLIR Thermal Studio Starter, and printed documentation

Operating Lifetime (hours):	
4 hours	
Field of View (°):	
33° × 25°	

Physical & Mechanical Properties

Weight (g):	
0.610 kg (1.34 lbs)	
Dimensions (mm):	
244 × 95 × 140 mm (9.6 × 3.7 × 5.5 in)	

Accuracy (%):

±2°C (±3.6°F) or ±2% of reading, for ambient temperature 10°C to 35°C (50°F to 95°F) and object temperature above 0°C (32°F)

Optical Properties

Resolution:	
5 MP	
Color:	
Iron, White hot, Black hot, Rainbow, Arctic, Lava, Rainbow HC	

Spectral Range:

7.5–13 μm

Electrical

Frequency (Hz):	
9 Hz	

Hardware & Interface Connectivity

Connector:	
Battery is charged inside the camera or in specific charger.	

Environmental & Durability Factors

Operating Temperature (°C):	
-15°C to 50°C (5°F to 122°F)	
Storage Temperature (°C):	
-40°C to 70°C (-40°F to 158°F)	

Shock Rating:	
25 g (IEC 60068-2-27)	
Vibration:	
2 g (IEC 60068-2-6)	

Regulatory Compliance

Certificate of Conformance:	
View	

Product Details

- Professional-Grade thermal Imagers for Industrial Applications
- Rugged, Handheld Design for Field Use
- Wide Temperature Ranges up to 550°C (1022°F)
- Wi-Fi for Fast Image Transfer and Reporting

The FLIR ExSeries delivers professional-grade thermal imaging in a rugged, handheld design built for demanding field environments. Offering industry-leading infrared resolution and wide temperature measurement ranges up to 550°C (1022°F), the E5 Pro, E6 Pro, and E8 Pro models are ideal for maintenance, building inspections, electrical diagnostics, HVAC servicing, and industrial troubleshooting. The E5 Pro (160 × 120 resolution) provides reliable thermal imaging for general inspections, the E6 Pro (240 × 180 resolution) offers enhanced resolution for identifying smaller temperature variations, and the E8 Pro (320 × 240 resolution) delivers the highest clarity and thermal sensitivity for advanced diagnostics. Built-in Wi-Fi connectivity allows for fast image transfer, reporting, and data sharing directly from the field, streamlining workflows and improving efficiency. With precision thermal sensitivity down to 0.04°C on the E8 Pro, users can detect subtle heat patterns and prevent equipment failures before they occur. The ExSeries combines FLIR's trusted infrared technology with durability and portability, making it a top choice for professional thermal imaging applications.

Model	E5 Pro	E6 Pro	E8 Pro
Resolution	160 × 120 (19,200 pixels)	240 × 180 pixels (43,200 pixels)	160 x 120 (19,200 pixels)
Temp Range	-20°C to 400°C (-4°F to 752°F)	-20°C to 550°C (-4°F to 1022°F)	-20°C to 550°C (-4°F to 1022°F)
Thermal sensitivity	<0.06°C	<0.05°C	<0.04°C

Accuracy: ±2°C (±3.6°F) or ±2% of reading, for ambient temperature 10°C to 35°C (50°F to 95°F) and object temperature above 0°C (32°F)