


# Glan-Thompson Polarizer 350 - 2200nm, 8mm



Glan-Thompson Polarizer

Stock **#89-544** 1 In Stock

-

1

+

€790<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €790,00 each                  |
| Qty 6+         | €755,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Physical & Mechanical Properties

8.0

Clear Aperture CA (mm):

25.40

Diameter (mm):

|                                          |                                                       |
|------------------------------------------|-------------------------------------------------------|
| 28.00                                    | Length (mm):                                          |
| Crystalline Glan-Thompson Polarizer      | Construction:                                         |
| Optical Properties                       |                                                       |
| Single Layer MgF <sub>2</sub>            | Coating:                                              |
| <5 x 10 <sup>-5</sup>                    | Extinction Ratio:                                     |
| Calcite                                  | Substrate: <input type="checkbox"/>                   |
| 20-10                                    | Surface Quality:                                      |
| λ/2 @ 632.8nm                            | Transmitted Wavefront, P-V:                           |
| <3                                       | Beam Deviation (arcmin):                              |
| λ/4 @ 632.8 nm                           | Transmitted Wavefront Distortion (RMS):               |
| 350 - 2200                               | Wavelength Range (nm):                                |
| 1 J/cm <sup>2</sup> @ 1064nm, 10ns, 10Hz | Damage Threshold, By Design: <input type="checkbox"/> |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 247:                  |

Product Details

- High Extinction Ratios up to 200 000:1
- High Laser Damage Thresholds up to 5 J/cm<sup>2</sup> @ 1064nm


Glan-Type Polarizers are mounted, polarizing prisms used in applications that require broad spectral ranges, high extinction ratios, or high polarization purities. Glan-Taylor Polarizers are medium-power, air-spaced UV to NIR polarizers that transmit the extraordinary beam. The ordinary beam is then reflected and absorbed by black glass plates that have been cemented to the prism. Glan-Laser Polarizers are similar to Glan-Taylor, but are designed for higher power applications and appropriate for use in Q-switched laser cavities. Glan-Laser Polarizers utilize an advanced polishing technique for minimizing surface scatter and feature two escape windows for passing the high power rejected light. Glan-Thompson Polarizers are low power polarizers that are ideal for UV, visible, or NIR applications, feature a cemented design, and transmit the extraordinary beam while absorbing the reflected ordinary beam.

LASER OPTICS

MADE BY EDMUND OPTICS®

LEARN MORE


Technical Information



Glan-Taylor Polarizers



Glan-Laser Polarizers



Glan-Thompson Polarizers