

[All Products](#) / [Optics](#) / [Windows](#) / [SCHOTT Chalcogenide Window](#)

[See all 11 Products in Family](#)


# Chalcogenide Glass

See More by [SCHOTT Optical Components](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



Stock #73-743 **NEW** 15 In Stock

1

€265<sup>,00</sup>

ADD TO CART

Volume Pricing	
Qty 1-25	€265,00 each
Qty 26-49	€212,00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

Material Safety Data Sheet:pdf

[Download All](#)

## General

**Type:** IR Window

**Note:** Edge chips outside of clear aperture <0.25

## Physical & Mechanical Properties

**Diameter (mm):** 10.00 ± 0.1

**Thickness (mm):** 1.50 ± 0.1

**Bevel:** Protective as needed

**Edges:** Fine Ground

**Young's Modulus (GPa):** 18.3

## Optical Properties

**Coating:** Uncoated

**Substrate:** SCHOTT IRG26

**Index of Refraction (n<sub>d</sub>):** 2.9316 @ 1µm  
2.7909 @ 5µm  
2.7781 @ 10µm

**Surface Quality:** 60-40

**Wavelength Range (nm):** 1000 - 14000

## Material Properties

**Density (g/cm<sup>3</sup>):** 4.63

**Transformation Temperature (°C):** 185

**Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):** 21.4 x 10<sup>-6</sup>/K (20 - 100°C)

## Regulatory Compliance

## Product Details

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

- SCHOTT IRG Infrared Glasses
- Lightweight with Broad Transmission Band
- Ideal Alternative to Germanium


SCHOTT Chalcogenide Glass Windows are suitable for a large range of IR applications and are an ideal alternative to Germanium substrates. Available in 5 different glass types optimized for excellent transmission in the NIR-LWIR ranges, these windows feature low dn/dt and dispersion with high color correction. Low density, coefficient of thermal expansion, and chemical resistance make them a great choice for low SWaP applications and harsh environments with changing temperatures. SCHOTT Chalcogenide Glass Windows are available in a variety of diameters and thicknesses. These windows are ideal for ideal for thermal imaging, spectroscopy, and sensing applications.

**Note:** Gloves must be worn while handling all IRG materials. IRG27 is a toxic material that can be absorbed through the skin. For all IRG materials, care should be taken when handling as these materials are soft and susceptible to scratches. These materials should be stored in a low humidity environment and extended exposure to UV light should be avoided to avoid the development of haziness on the surface of the optic. Contact with high temperatures or strong acids or bases should be avoided.

- IRG22 – Offers excellent transmission in the NIR range. Chemical Formula  $\text{Ge}_{33}\text{As}_{12}\text{Se}_{55}$
- IRG24 – Offers a low coefficient of thermal expansion for heat-sensitive applications. Chemical Formula  $\text{Ge}_{10}\text{As}_{40}\text{Se}_{50}$
- IRG25 – Offers excellent SWIR, MWIR, and LWIR transmission. Chemical Formula  $\text{Ge}_{28}\text{Sb}_{12}\text{Se}_{60}$
- IRG26 – Offers an exceptionally broad transmission range, with minimal absorption at 12.5um. Germanium Free. Chemical Formula  $\text{As}_{40}\text{Se}_{60}$
- IRG27 – Combines a high SWIR/MWIR transmission with a low coefficient of thermal expansion. Germanium Free. Chemical Formula  $\text{As}_2\text{S}_3$

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



**Component Handling Tools**