

[See all 1 Products in Family](#)

# Coherent® LaserCheck™ 1098293

See More by [Coherent®](#)



Coherent® LaserCheck™, #12-394

Stock #12-394 **10 In Stock**

€600<sup>.00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€600,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

SCHOTT NG-9, 1 mm thick	<b>Filters Included :</b>
NG-10 Schott ND Filter, 1mm Thickness	<b>Type of Optics:</b>
0.78	<b>Depth (inches):</b>
2 - 10	<b>Response Time (ms):</b>

Meter Accuracy (%):

±5

Power Resolution (µW):

0.01

## Physical & Mechanical Properties

Active Area Diameter (mm):

8.0

Length (inches):

6.59

Weight (g):

44

Width (inches):

0.92

## Optical Properties

Spectral Response (nm):

400 - 1064

## Sensor

Type of Sensor:

Silicon Cell

## Electrical

Incident Power Density (W/cm<sup>2</sup>):

Without Filter: 0.5

With Filter: 30

Incident Power (mW):

Without Filter: 0.005 - 10

With Filter: 0.005 - 1000

Minimum Incident Beam Power (µW):

3 - 10

## Hardware & Interface Connectivity

Power Supply:

Battery, Lifetime: 180,000 Samples @ 12 seconds/sample

## Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

## Product Details

- 0.5µW to 1W
- 400nm to 1064nm
- ±8% Accuracy

This laser power meter is truly a technological breakthrough for users of low power CW lasers! This is the most versatile, compact, and affordable laser power meter available today. Controls and indicators: power/wavelength display select switch, wavelength select increment and decrement buttons, sample/hold button, 3-digit LCD with units indicator, attenuator position indicator, attenuator position control slide and over-range tone generator. Automatic functions: power range, wavelength correction, peak sample & hold, shut-off, over-range detect, and attenuator position detect. Additional features include an over-range indication, pocket clip, and storage case.

**Note:** Battery is not replaceable.