

# Coherent® PowerMax USB PM10-19C Measurement System 1168344 | 10W

See More by [Coherent®](#)



Stock #12-409 [CONTACT US](#)

⊖ 1 ⊕ €1.605<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€1.605,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Model Number:**  
PM10-19C  
Coherent Part Number: 1168344

**Type:**  
Meterless

**Calibration Uncertainty (%):**  
±2

0.5 - 10 **Long Pulse Joule Mode Range (J):**

Water/Air (intermittent) **Cooling Method:**

0.6 @ 1064nm, 10ns **Maximum Incident Energy Density (J/cm<sup>2</sup>):**

## Physical & Mechanical Properties

19 **Active Area Diameter (mm):**

## Optical Properties

10600 **Calibration Wavelength (nm):**

190 - 11000 **Wavelength Range (nm):**

0.19 - 11 **Wavelength Range (μm):**

## Sensor

Thermopile **Type of Sensor:**

## Electrical

±1.5 **Spectral Compensation Accuracy (%):**

30 (air-cooled) **Maximum Intermittent Power, <5min (W):**

6 **Maximum Incident Power Density (kW/cm<sup>2</sup>):**

10mW - 10W **Power Range:**

## Hardware & Interface Connectivity

2.5 **Length of Cable (m):**

USB **Computer Interface:**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[Contains SVHC\(s\)](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

## Product Details

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.