

[See all 78 Products in Family](#)

## Preloaded Norland Optical Adhesive NOA 170 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)



Stock #12-850 **2 In Stock**

- 1 + €102.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-11	€102,00 each
Qty 12-19	€91,80 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

0.34 **Size (oz):**

170 **Norland Number:**

**Shelf Life:**

4 months

Barrel **Type:**

**Typical Applications:**  
High refractive index adhesive with higher viscosity for bonding glass or plastics. Contains nanoparticles.

Contains 10g of adhesive **Note:**

### Optical Properties

1.70 @ 589nm **Index of Refraction (n<sub>d</sub>):**

315 - 450 **Absorption Range (nm):**

### Material Properties

Excellent **Glass Bonding:**

Good **Metal Bonding:**

Excellent **Plastic Bonding:**

4500 - 5500 **Viscosity (cps):**

Glass to Glass **Bonding Type:**

6 **Energy for Full Cure (J/cm<sup>2</sup>):**

### Environmental & Durability Factors

Hard & Brittle **Durability:**

### Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 253:**

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

