

Dual Axis Linear Scale Micrometer



Stock #58-608 [CONTACT US](#)

- 1 + €665⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€665,00 each
Qty 5+	€632,30 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

No **NST Certification:**

Physical & Mechanical Properties

Metric: 25µm
English: 1 mil (0.001") **Scale Divisions:**

25.4 x 76.2 **Dimensions (mm):**

Thickness (mm):
1.50 ±0.100

Dimensional Tolerance (mm):
±0.100

Optical Properties

Chrome on Glass Substrate: □

60-40 Surface Quality:

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 235:

Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

Technical Information

