

[See all 14 Products in Family](#)

# LightPath 390010 | 4.5mm Dia., 0.83 NA, BBAR (8000-12000nm), Molded IR Aspheric Lens

See More by [Lightpath®](#)



Stock #88-073 **2 In Stock**

⊖ 1 ⊕ €410<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€410,00 each
Qty 11-49	€369,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

390010 **Lightpath Lens Code:**

Aspheric Lens **Type:**

### Physical & Mechanical Properties

4.50 ±0.015 **Diameter (mm):**

3.00	Clear Aperture CA (mm):
1.63	Edge Thickness ET (mm):
2.17	Center Thickness CT (mm):
	Bevel:
Protective as needed	

## Optical Properties

1.47 @ 9200nm	Effective Focal Length EFL (mm):
0.83	Numerical Aperture NA:
Black Diamond™ BD-2 (Ge <sub>26</sub> Sb <sub>12</sub> Se <sub>60</sub> )	Substrate: <input type="checkbox"/>
9200	Aspheric Design Wavelength (nm):
BBAR (8000-12000nm)	Coating:
R <sub>avg</sub> <1.0% @ 8 - 12μm	Coating Specification:
80-50	Surface Quality:
0.6	f#:
2.6023	Index of Refraction (n <sub>d</sub> ) @ 10μm:
2.5843	Index of Refraction (n <sub>d</sub> ) @ 14μm:
2.6210	Index of Refraction (n <sub>d</sub> ) @ 4μm:
2.6173	Index of Refraction (n <sub>d</sub> ) @ 5μm:
8000 - 12000	Wavelength Range (nm):
0.63	Working Distance (mm):
Infinite	Conjugate Distance:
9200	Focal Length Specification Wavelength (nm):

## Material Properties

14.00	Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C):
4.68	Density (g/cm <sup>3</sup> ):
70 x 10 <sup>-6</sup> /°C from -40° to +80°C (5 - 14 μm)	Thermo-optic coefficient dn/dT:
285.00	Transformation Temperature (°C):

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 247:

## Product Details

- Wavelength Range of 1.8 - 12μm
- Variety of Coating Options
- Mounted and Unmounted Versions

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses feature a low-cost, molded design and offer several key benefits over Germanium substrate aspheres. With a dn/dT and CTE significantly less than that of Germanium, the lenses feature a smaller change in focal length as a function of temperature change. Featuring a higher operating temperature than Germanium (which suffers 20 – 30% transmission loss at 100°C), the lenses can be used in applications including collimators for QCL lasers and as components within thermal imaging assemblies. LightPath Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses have a wavelength range of 1.8 - 12μm. These lenses are available mounted or unmounted, in a variety of coating options.

## Technical Information

8.0 - 12 $\mu$ m AR Coating

