

Fiber Spatial Filter-FC



Fiber Spatial Filter-FC, #55-475

Stock **#55-475 2 In Stock**

-

1

+

€1.310⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.310,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Adjustable - Linear (XYZ) & Tip-Tilt	Type:
Fiber Connector	Type of Optics:
10Xmicroscope objective included	Note:
Physical & Mechanical Properties	
	Construction:

Black Anodized Aluminum	
Linear Travel (mm):	
XY: ±1.5, Z: ±5	
Linear Travel Resolution (µm):	
2.5 (XY)	
Tip/Tilt Angle (°):	
±2	
Base Tilt Angle (°):	
±2	
Electrical	
Fiber Connection:	
FC	
Hardware & Interface Connectivity	
Type of Drive:	
Differential Micrometer (XY)	
Threading & Mounting	
Compatible Post:	
M6 x 1.0	
Regulatory Compliance	
RoHS 2015:	
Exempt	
Certificate of Conformance:	
View	
Reach 247:	
Contains SVHC(s)	

Product Details

- X-Y Micrometer Translation
- Gimbal Tilt Control for Fiber Alignment
- Z-Axis Translation for Objective Mount

Our Metric Spatial Filters are designed to ease [fiber optic](#) and [pinhole](#) system integration. With ±1.5mm micrometer driven X-Y translation, 2.5µm resolution, and an objective mount with 10mm Z-axis translation, these Metric Spatial Filters are ideal for a range of DIN and JIS standard [objectives](#). The fiber optic metric spatial filter provides easy connection for fiber optics with an FC termination and features gimbal tilt control for fiber alignment with a ±2° adjustable angle range. The pinhole metric spatial filter includes a pinhole adapter for integrating mounted and unmounted pinholes.

Note: Metric Spatial Filters are only compatible with the following objectives: DIN Achromatic 4X([#43-902](#)), DIN Plan 4X([#67-706](#)), and the JIS Achromatic 10X.

Technical Information

