


Film-Format Achromatic Polymer Retarder $\lambda/2$ 25.4mm Dia AR



Stock **#70-576** 8 In Stock

-

1

+

€735^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	€735,00 each
Qty 11-25	€555,00 each
Qty 26+	€515,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Note:

Slow axis marked with blue dot on part and stripe on protective film

Physical & Mechanical Properties	
25.40 +/- 0.15	Diameter (mm):
0.35 Nominal	Thickness (mm):
Optical Properties	
±10	Angle of Incidence (°):
Polymer Stack	Substrate: ☐
$\lambda/2 \pm \lambda/100$	Retardance:
60-40	Surface Quality:
BBAR: R<= 0.75% @700-1100nm (per surface)	Coating Specification:
700 - 1100	Wavelength Range (nm):
500 Watt/cm ² CW, .3 J/cm ² 10 nsec pulses @ 532nm, 2 J/cm ² 20 nsec pulses @ 1064nm typical	Damage Threshold, By Design: ☐
Anti-Reflection (both sides)	Coating Type:
Environmental & Durability Factors	
-20 to +40	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

PRODUCT DETAILS

- Ultra-Thin ≤0.55mm Substrates for OEM Integration
- Options For 600-1100nm and 700-1550nm
- Wide Acceptance Angle Tolerance of ±10°

Ultra-Thin NIR Achromatic Polymer Retarders feature an optically fused and adhesive-free construction, allowing for high temperature resistance, high transmission, and an ultra-thin format. These retarders are designed with a multi-layer polymer stack and feature a 0.35mm thickness for $\lambda/2$ retarders and 0.55mm thickness for $\lambda/4$ retarders. Available either uncoated or with an AR-Coating, these retarders offer a retardance tolerance of $\lambda/100$ in the NIR range at a wide range of angles of incidence. Uncoated Ultra-Thin NIR Achromatic Polymer Retarders offer an increased retardance range of 700-1550nm while the coated options feature improved transmission from 700-1100nm. These waveplates are ideal for NIR imaging and analytical instrumentation, as well as OEM integration and other applications requiring a small form factor.