

FLIR E6 Pro Thermal Imaging Camera



Stock **#75-074** NEW **1 In Stock**

-

1

+

€2.150⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.150,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Ex Series

Model Number:

Contents of Kit:

Infrared camera (with LED flashlight), hard transport case, battery (inside camera), power supply (with EU, UK, US and AU plugs), FLIR

Thermal Studio Starter, and printed documentation	
4 hours	Operating Lifetime (hours):
33° × 25°	Field of View (°):
Standard Measurement Temperature (°C): -20°C to 550°C (-4°F to 1022°F) in two ranges	
Thermal	Spectrum:

Physical & Mechanical Properties

0.610 kg (1.34 lbs)	Weight (g):
244 × 95 × 140 mm (9.6 × 3.7 × 5.5 in)	Dimensions (mm):
Accuracy (%): ±2°C (±3.6°F) or ±2% of reading, for ambient temperature 10°C to 35°C (50°F to 95°F) and object temperature above 0°C (32°F)	

Optical Properties

5 MP	Resolution:
Iron, White hot, Black hot, Rainbow, Arctic, Lava, Rainbow HC	Color:

Electrical

9 Hz	Frequency (Hz):
------	-----------------

Hardware & Interface Connectivity

Battery is charged inside the camera or in specific charger.	Connector:
--	------------

Environmental & Durability Factors

-15°C to 50°C (5°F to 122°F)	Operating Temperature (°C):
-40°C to 70°C (-40°F to 158°F)	Storage Temperature (°C):
25 g (IEC 60068-2-27)	Shock Rating:
2 g (IEC 60068-2-6)	Vibration:

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

PRODUCT DETAILS

- Professional-Grade thermal Imagers for Industrial Applications
- Rugged, Handheld Design for Field Use
- Wide Temperature Ranges up to 550°C (1022°F)
- Wi-Fi for Fast Image Transfer and Reporting

The FLIR Ex Series delivers professional-grade thermal imaging in a rugged, handheld design built for demanding field environments. Offering industry-leading infrared resolution and wide temperature measurement ranges up to 550°C (1022°F), the E5 Pro, E6 Pro, and E8 Pro models are ideal for maintenance, building inspections, electrical diagnostics, HVAC servicing, and industrial troubleshooting. The E5 Pro (160 × 120 resolution) provides reliable thermal imaging for general inspections, the E6 Pro (240 × 180 resolution) offers enhanced resolution for identifying smaller temperature variations, and the E8 Pro (320 × 240 resolution) delivers the highest clarity and thermal sensitivity for advanced diagnostics. Built-in Wi-Fi connectivity allows for fast image transfer, reporting, and data sharing directly from the field, streamlining workflows and improving efficiency. With precision thermal sensitivity down to 0.04°C on the E8 Pro, users can detect subtle heat patterns and prevent equipment failures before they occur. The Ex Series combines FLIR's trusted infrared technology with durability and portability, making it a top choice for professional thermal imaging applications.

Model	E5 Pro	E6 Pro	E8 Pro
Resolution	160 × 120 (19,200 pixels)	240 × 180 pixels (43,200 pixels)	160 x 120 (19,200 pixels)
Temp Range	-20°C to 400°C (-4°F to 752°F)	-20°C to 550°C (-4°F to 1022°F)	-20°C to 550°C (-4°F to 1022°F)
Thermal sensitivity	<0.06°C	<0.05°C	<0.04°C

Accuracy: ±2°C (±3.6°F) or ±2% of reading, for ambient temperature 10°C to 35°C (50°F to 95°F) and object temperature above 0°C (32°F)