

[See all 7 Products in Family](#)

L2-GC-04K03N-00, DALSA Linea2 Multispectral Line Scan 5GigE Camera

See More by [Teledyne DALSA](#)



Teledyne Imaging DALSA Linea2 5GigE Line Scan Cameras - Front



Stock #71-785 **2 In Stock**

- 1 + €2.520⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.520,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Multispectral **Spectrum:**

General

Multispectral **Type:**

L2-GC-04K03N-00 **Model Number:**

Teledyne DALSA	Manufacturer:
LINEA2™	Camera Series:
4096 x 4	Resolution (Pixels):
Physical & Mechanical Properties	
62 x 62 x 49.3 (excludes connectors and lens mount)	Dimensions (mm):
<280	Weight (g):
Full	Housing:
Sensor	
7.00 x 7.00	Pixel Size, H x V (µm):
DALSA Line Scan CMOS	Type of Sensor:
8/12 bit	Pixel Depth:
71.00	Dynamic Range (dB):
GigE Vision	Machine Vision Standard:
9.5	Read Noise (e⁻):
32 (x4 RGB + NIR)	Maximum Line Rate (kHz):
32	Full Well Depth (ke⁻):
Electrical	
13	Power Consumption (W):
Hardware & Interface Connectivity	
5GigE (PoE)	Interface:
5GigE, RJ45 with Screw Locks	Connector:
+12 to +24V DC HD15 Connector or 48V POE	Power Supply:
Back Panel	Interface Port Orientation:
HD15 (High Density)	GPIO Connector Type:
Threading & Mounting	
M42-Mount	Mount:
Environmental & Durability Factors	
-10 to +65	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Color and Multispectral Options Available
- Line Rates of 32 or 40kHz
- Simple Integration with 5Gbase-T (5GigE) Ethernet Connectivity
- 4k Resolution Option Available

Teledyne Imaging DALSA Linea2 5GigE Line Scan Cameras utilize a single line of sensor pixels to build up a two-dimensional image at a lower cost than area scan cameras. The color camera features a line rate of 40kHz and a resolution of 4096 x 3 with 7µm pixels, whereas the multispectral camera features a line rate of 32kHz with a resolution of 4096 x 4 and 7µm pixels. The high framerates and dedicated RGB and NIR channels enable the detection of sensitive color differences in high-speed applications. Teledyne Imaging DALSA Linea2 5GigE Line Scan Cameras are ideal for automated optical inspections, sorting systems, materials grading and inspections, and general-purpose machine vision applications. The multispectral cameras include sensors that can capture RGB color and NIR in a single scan with minimal spectral crosstalk between the color and NIR channels due to their unique wafer-level dichroic filter coating. Download this [whitepaper](#) for more information on applications that would benefit from line scan camera technology.

Note: An H15 cable is required for GPIO operation and is not included with these cameras.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™,

