

Fly's Eye Array 10 x 10mm, 250µm Pitch, 5° Divergence



Microlens Arrays



Stock **#64-489** ☐ In Stock

1

€705,00

ADD TO CART

Qty 1-10
€705,00

Qty 11+
€620,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
1.60

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating: Uncoated
Type: Flys Eye Lens Array
Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±5
Lens Profile: Spherical
Pitch (µm): 250.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 0.75
Thickness (mm): 2.25
Thickness Tolerance (mm): ±0.05
Type of Optics: Double-Convex

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View