

[See all 76 Products in Family](#)

LightPath 355198 | 1.4mm Dia., 0.50 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#16-704** 13 In Stock

-

1

+

€75^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	€75,00 each
Qty 11-49	€67,50 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
355198	Lightpath Lens Code:
Aspheric Lens	Type:
Collimate or Focus Laser Light	Typical Applications:

Physical & Mechanical Properties	
1.40 ±0.015	Diameter (mm):
1.1	Clear Aperture CA (mm):
0.50	Edge Thickness ET (mm):
0.71 ±0.03	Center Thickness CT (mm):
Protective as needed	Bevel:

Optical Properties	
1.05 @ 1550nm	Effective Focal Length EFL (mm):
0.50	Numerical Aperture NA:
D-ZLaF52LA	Substrate: 
±1	Focal Length Tolerance (%):
1550	Aspheric Design Wavelength (nm):
BBAR (1050-1600nm)	Coating:
R _{abs} <1.0% @ 1050 - 1600nm	Coating Specification:
40-20	Surface Quality:
1.00	f/#:
1050 - 1600	Wavelength Range (nm):
0.61	Working Distance (mm):
Infinite	Conjugate Distance:
<0.150	Transmitted Wavefront Error (λ, RMS):

Environmental & Durability Factors	
≤200	Operating Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



;