

# LUCID Vision Labs Atlas10 ATX204S-CC, Sony IMX531, 20.4MP, Color Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Atlas10 10GigE Power over Ethernet (PoE) Cameras (Front, C-Mount)



Stock #17-117 3-4 DAYS

- 1 + **€4.394,00**

ADD TO CART

Qty 1+

€4.394,00

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

**Video Output:**  
10GigE (PoE+)

**Type:**  
Color Camera

|                                                                                                                                                                                                                                   |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Manufacturer:</b><br>Lucid Vision Labs                                                                                                                                                                                         |
| <b>Mounting Threads:</b><br>2 x ¼-20 with Tripod Mount Adapter <a href="#">#17-120</a>                                                                                                                                            |
| <b>Image Buffer:</b><br>380MB                                                                                                                                                                                                     |
| <b>Camera Family:</b><br>Atlas10                                                                                                                                                                                                  |
| <b>Model Number:</b><br>ATX204S-CC                                                                                                                                                                                                |
| <b>Imaging Sensor:</b><br>Sony IMX531                                                                                                                                                                                             |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                                                                                                                                                                   |
| <b>Type of Shutter:</b><br>Global                                                                                                                                                                                                 |
| <b>Camera Sensor Format:</b><br>1.1"                                                                                                                                                                                              |
| <b>Resolution (MegaPixels):</b><br>20.40                                                                                                                                                                                          |
| <b>Pixels (H x V):</b><br>4,504 x 4,504                                                                                                                                                                                           |
| <b>Pixel Size, H x V (µm):</b><br>2.74 x 2.74                                                                                                                                                                                     |
| <b>Sensing Area, H x V (mm):</b><br>12.34 x 12.34                                                                                                                                                                                 |
| <b>Frame Rate (fps):</b><br>61.00                                                                                                                                                                                                 |
| <b>Pixel Depth:</b><br>8/10/12 bit                                                                                                                                                                                                |
| <b>Exposure Time:</b><br>6.24µs - 10s                                                                                                                                                                                             |
| <b>Connector:</b><br>10GigE, M12                                                                                                                                                                                                  |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately:<br>USA: <a href="#">#18-364</a><br>Europe: <a href="#">#18-364</a><br>Japan: <a href="#">#18-364</a><br>Korea: Not Available<br>China: <a href="#">#18-364</a> |
| <b>Power Consumption (W):</b><br>11.5 (External Power Supply)<br><12 (PoE+)                                                                                                                                                       |
| <b>GPIOs:</b><br>1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports                                                                                                                               |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)                                                                                                                                          |
| <b>Dimensions (mm):</b><br>55 x 55 x 95.5 (excludes connectors and lens mount)                                                                                                                                                    |
| <b>Weight (g):</b><br>304                                                                                                                                                                                                         |
| <b>Mount:</b><br>C-Mount                                                                                                                                                                                                          |
| <b>Housing:</b><br>Full                                                                                                                                                                                                           |
| <b>Interface Port Orientation:</b><br>Back Panel                                                                                                                                                                                  |
| <b>Dynamic Range (dB):</b><br>70.7                                                                                                                                                                                                |
| <b>Operating Temperature (°C):</b><br>-20 to +55                                                                                                                                                                                  |
| <b>Storage Temperature (°C):</b><br>-30 to +60                                                                                                                                                                                    |
| <b>GPIO Connector Type:</b><br>8-pin M8                                                                                                                                                                                           |
| <b>Machine Vision Standard:</b><br>GigE Vision v2.0                                                                                                                                                                               |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

