

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

See More by [LUCID Vision Labs™](#)



Stock #23-971 3-4 DAYS



1



€2.965,00

ADD TO CART

Qty 1+

€2.965,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:

GigE (PoE)

Type:

Monochrome Camera

Manufacturer:

Lucid Vision Labs

Image Buffer: 380 MB
Camera Family: Atlas IP67
Model Number: ATP162S-MC
Imaging Sensor: Sony IMX542
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 16.20
Pixels (H x V): 5,320 x 3,032
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 14.58 x 8.31
Frame Rate (fps): 34.40
Pixel Depth: 8/10/12 Bit
Exposure Time: 12.12 µs to 10 s (Normal) / 2.29 µs to 2.46 µs (Short Mode)
Connector: PoE, M12
Power Supply: PoE (IEEE 802.3af), or 12-24 VDC external
Power Consumption (W): 8W via PoE, 7W when powered externally
GPIOs: 1 opto-isolated input, 1 opto-isolated out, 2 non-isolated bi-directional ports
Synchronization: Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)
Dimensions (mm): 60 x 60 x 65
Weight (g): 340
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): -20 to 55
Storage Temperature (°C): -30 to 60
GPIO Connector Type: 8 pin M8 connector
Machine Vision Standard: GigE Vision v2.0

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View