


Two IDS industrial cameras are shown. The camera on the left has a purple lens and the camera on the right has a blue lens. Both cameras are black with a silver-colored mounting bracket. The IDS logo is visible on the side of each camera. They are mounted on a black base.



☐ -    1    ☐ +    €700<sup>,00</sup>

[ADD TO CART](#)

! Prices shown are exclusive of VAT/local taxes

## Product Downloads

**Spectrum:**

| General |  |
|---------|--|
|---------|--|

Type:

**Model Number:**

|                                                                     |                             |
|---------------------------------------------------------------------|-----------------------------|
| IDS Imaging Development Systems                                     | Manufacturer:               |
| uEye+ SE                                                            | Camera Series:              |
| Physical & Mechanical Properties                                    |                             |
| 34 x44 x47 (excludes connectors and lens mount)                     | Dimensions (mm):            |
| 106                                                                 | Weight (g):                 |
| Full                                                                | Housing:                    |
| Sensor                                                              |                             |
| 128MB                                                               | Image Buffer:               |
| 1/1.8"                                                              | Sensor Format:              |
| 6.41                                                                | Resolution (Megapixels):    |
| 18.00                                                               | Frame Rate (fps):           |
| 3,088 x2,076                                                        | Pixels (H x V):             |
| 2.40 x2.40                                                          | Pixel Size, H x V (µm):     |
| 7.411 x4.982                                                        | Sensing Area, H x V (mm):   |
| Sony IMX178                                                         | Imaging Sensor:             |
| Progressive Scan CMOS                                               | Type of Sensor:             |
| Rolling                                                             | Shutter Type:               |
| 12 bit                                                              | Pixel Depth:                |
| 0.013ms - 2000ms                                                    | Exposure Time:              |
| 71.00                                                               | Dynamic Range (dB):         |
| GigE Vision                                                         | Machine Vision Standard:    |
| Electrical                                                          |                             |
| 1.8 - 2.7                                                           | Power Consumption (W):      |
| Hardware & Interface Connectivity                                   |                             |
| GigE (PoE)                                                          | Interface:                  |
| GigE RJ45, screwable                                                | Connector:                  |
| Power over Ethernet (PoE) or 12 - 24VDC via GPIO with #16-016       | Power Supply:               |
| 2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground | GPIOs:                      |
| Hardware Trigger (GPIO); Software Trigger                           | Synchronization:            |
| Back Panel                                                          | Interface Port Orientation: |
| 8-pin Hirose connector (HR25-7TR-8PA(73))                           | GPIO Connector Type:        |
| Threading & Mounting                                                |                             |
| C-Mount                                                             | Mount:                      |
| 1/4-20 with Tripod Mount Adapter #16-017                            | Mounting Threads:           |
| Environmental & Durability Factors                                  |                             |
| 0 to +55                                                            | Operating Temperature (°C): |
| -20 to +60                                                          | Storage Temperature (°C):   |

| Regulatory Compliance            |                             |
|----------------------------------|-----------------------------|
| <a href="#">Exempt</a>           | RoHS 2015:                  |
| <a href="#">View</a>             | Certificate of Conformance: |
| <a href="#">Contains SVHC(s)</a> | REACH 241:                  |

## Product Details

- Standard (SE) and Compact (CP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- GenICam GigE Vision Compliant
- [IDS Imaging uEye CP/XCP/SE USB3 Cameras](#) Available

IDS Imaging uEye CP/SE GigE Cameras utilize IDS Imaging's [peak SDK platform](#) that supports GenICam and GigE Vision standards for ease of software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat sensitive applications. IDS Imaging uEye CP/SE GigE Cameras feature a screwable 8-pin Hirose connector for trigger and flash as well as two GPIOs. These cameras are ideal for a variety of applications such as automation, automotive, medical technology, and logistics.