

[See all 28 Products in Family](#)

## M6x1.0 x 25mm SHCS, 50/Pack



Stock **#55-193** **1 In Stock**

-

1

+

€25<sup>.75</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | €25,75 each                   |
| Qty 10-24      | €23,25 each                   |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

### Product Details

- Ideal for Use with Our English Sized Positioning Equipment
- A Broad Selection of Sizes Available
- 50 Pieces per Package
- [Socket Head Cap Screw Kits](#) Available
- [Allen Wrenches](#) Also Available

Socket head cap screws offer a reliable, high-strength solution for mounting and assembling optical components in precision systems. Manufactured from durable alloy steel, these screws feature a sleek, consistent design that is ideal for use in many environments. The hexagonal socket head design allows for easy installation in tight spaces using standard [Allen Wrenches](#), ensuring repeatable, secure fastening without damaging surrounding optics or mounts.

Available in English and Metric threading and a variety of hex key sizes, these cap screws are perfect for integration with optical breadboards, translation stages, and custom assemblies. Whether you're building a prototype or maintaining alignment-critical systems, these versatile fasteners offer dependable performance and easy compatibility with Edmund Optics' mechanical components.

FAQ(s)

**What is a cap screw used for?**

Capscrews are used to fasten components securely in optical systems, mounts, and mechanical assemblies where precision and durability are necessary.

**What's the difference between a cap screw and a bolt?**

A cap screw is designed to fit tightly into a tapped hole and often provides a cleaner, more secure fit than a standard bolt. Unlike bolts which are tightened using a nut, socket head cap screws have a hexagonal socket making it easy to secure using an Allen wrench.

**What materials are these cap screws made of?**

Edmund Optics' cap screws are typically manufactured from alloy steel for corrosion resistance and strength in lab or production environments.

**Are socket head cap screws reusable?**

Yes, if not damaged or over-torqued, they can be reused repeatedly. Always check thread integrity and apply proper torque when reassembling.

Technical Information

|         | Allen Wrench Stock No.  | Allen Wrench Hex Key Size | For Socket Head Cap | For Socket Head Set | For Button Head Cap |
|---------|-------------------------|---------------------------|---------------------|---------------------|---------------------|
| English | <a href="#">#58-639</a> | 0.028"                    | N/A                 | #0                  | N/A                 |
|         | <a href="#">#58-638</a> | 0.035"                    | N/A                 | #2                  | #0                  |
|         | <a href="#">#56-271</a> | 0.050"                    | #0                  | #4                  | #2                  |
|         | <a href="#">#58-637</a> | 1/16"                     | #1                  | #6                  | #3 & #4             |
|         | <a href="#">#56-270</a> | 1/64"                     | #2 & #3             | #8                  | #5 & #6             |
|         | <a href="#">#55-188</a> | 3/32"                     | #4 & #5             | #10                 | #8                  |
|         | <a href="#">#55-189</a> | 7/64"                     | #6                  | N/A                 | N/A                 |
|         | <a href="#">#03-662</a> | 1/8"                      | N/A                 | 1/4"                | #10                 |
|         | <a href="#">#55-190</a> | 9/64"                     | #8                  | N/A                 | N/A                 |
|         | <a href="#">#55-191</a> | 5/32"                     | #10 & #12           | 5/16"               | #12 & 1/4"          |
|         | <a href="#">#55-192</a> | 3/16"                     | 1/4"                | 3/8"                | 5/16"               |
| Metric  | <a href="#">#58-636</a> | 0.9mm                     | N/A                 | M2                  | N/A                 |
|         | <a href="#">#55-452</a> | 1.5mm                     | M1.6 & M2           | M3                  | M2.5                |
|         | <a href="#">#57-445</a> | 2mm                       | M2.5 & M2.6         | M4                  | M3                  |
|         | <a href="#">#55-451</a> | 2.5mm                     | M3                  | M5                  | M4                  |
|         | <a href="#">#55-199</a> | 3mm                       | M4                  | M6                  | M5                  |
|         | <a href="#">#55-200</a> | 5mm                       | M6                  | M10                 | M8                  |