

## M77 x 0.75 Variable Neutral Density (ND) Filters



Variable Neutral Density (ND) Machine Vision Filter

Stock **#16-081** **5 In Stock**

-

1

+

€207<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | €207,00 each                  |
| Qty 10-25      | €192,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                          |                         |
|----------------------------------|-------------------------|
| Neutral Density Filter           | Type:                   |
| AR Coated                        | Note:                   |
| Physical & Mechanical Properties |                         |
| 72.5                             | Clear Aperture CA (mm): |

|                                                              |                                         |
|--------------------------------------------------------------|-----------------------------------------|
| 72.5                                                         | Clear Aperture (%):                     |
| Optical Properties                                           |                                         |
| Optical Density OD (Average):<br>0.5 - 4.0 @ 550 - 650nm     |                                         |
| Polymer Film XP42                                            | Substrate: <input type="checkbox"/>     |
| Blocking Wavelength Range (nm):<br>400 - 700                 |                                         |
| Coating Specification:<br>R <sub>avg</sub> ≤2% @ 400 - 700nm |                                         |
| Threading & Mounting                                         |                                         |
| M77 x0.75                                                    | Filter Thread:                          |
| 5.85                                                         | Mount Thickness (mm):                   |
| 80 ±0.2                                                      | Mount Diameter (mm):                    |
| 7.85                                                         | Mount Thickness Including Threads (mm): |
| Regulatory Compliance                                        |                                         |
| <a href="#">View</a>                                         | Certificate of Conformance:             |

## Product Details

- Continuous Attenuation of Illumination Intensity
  - Ideal for the Visible Spectrum
  - Variety of Common Machine Vision Threads Available
  - [Mounted Absorptive Neutral Density \(ND\) Filters](#) Also Available
- Variable Neutral Density (ND) Machine Vision Filters are designed for continuous attenuation of illumination intensity across the visible spectrum. Consisting of two linear polarizers ([XP42](#)) in an aluminum mount, one polarizer can be rotated with respect to the other and the transmitted light intensity can be adjusted. Variable Neutral Density (ND) Machine Vision Filters are available with common imaging lens filter threads to allow easy integration into machine vision or photography applications.