

[See all 14 Products in Family](#)

# LightPath 390036 | 6.5mm Dia., 0.56 NA, BBAR (1800-3000nm), Molded IR Aspheric Lens

See More by [Lightpath®](#)



Stock #66-560 **9 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €410<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€410,00 each
Qty 11-49	€369,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

390036 **Lightpath Lens Code:**

Aspheric Lens **Type:**

### Physical & Mechanical Properties

**Diameter (mm):**

6.50 ±0.015

Clear Aperture CA (mm):

5.00

Edge Thickness ET (mm):

1.94

Center Thickness CT (mm):

2.50

Bevel:

Protective as needed

## Optical Properties

Effective Focal Length EFL (mm):

4.00 @2500nm

Numerical Aperture NA:

0.56

Substrate: □

Black Diamond™ BD-2 (Ge<sub>26</sub>Sb<sub>12</sub>Se<sub>60</sub>)

Aspheric Design Wavelength (nm):

2500

Coating:

BBAR (1800-3000nm)

Coating Specification:

R<sub>avg</sub> <1.0% @ 1.8 - 3.0μm

Surface Quality:

80-50

f#:

0.89

Index of Refraction (n<sub>d</sub>) @ 10μm:

2.6023

Index of Refraction (n<sub>d</sub>) @ 14μm:

2.5843

Index of Refraction (n<sub>d</sub>) @ 4μm:

2.6210

Index of Refraction (n<sub>d</sub>) @ 5μm:

2.6173

Wavelength Range (nm):

1800 - 3000

Working Distance (mm):

3.05

Conjugate Distance:

Infinite

Focal Length Specification Wavelength (nm):

2500

## Material Properties

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):

14.00

Density (g/cm<sup>3</sup>):

4.68

Thermo-optic coefficient dn/dT:

70 x 10<sup>-6</sup>/°C from -40° to +80°C (5 - 14 μm)

Transformation Temperature (°C):

285.00

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:


[Compliant](#)

## Product Details

- Wavelength Range of 1.8 - 12μm
- Variety of Coating Options
- Mounted and Unmounted Versions

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses feature a low-cost, molded design and offer several key benefits over Germanium substrate aspheres. With a dn/dT and CTE significantly less than that of Germanium, the lenses feature a smaller change in focal length as a function of temperature change. Featuring a higher operating temperature than Germanium (which suffers 20 – 30% transmission loss at 100°C), the lenses can be used in applications including collimators for QCL lasers and as components within thermal imaging assemblies. LightPath Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses have a wavelength range of 1.8 - 12μm. These lenses are available mounted or unmounted, in a variety of coating options.

## Technical Information



## Compatible Mounts

---