

[See all 20 Products in Family](#)

InGaAs Variable Gain Photoreceiver, 800-1700nm



Stock **#90-629** NEW **1 In Stock**

⊖ 1 ⊕ €4.400⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | €4.400,00 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Remote Control:
Yes

Includes:
LEMO® 3-pin connector
Datasheet

Note:

Physical & Mechanical Properties

Weight (g):
320

Case Size: 170 x 60 x 45

Dimensions (mm):

Optical Properties

800 - 1700 nm

Spectral Range:

Sensor

InGaAs PIN

Detector Type:

Electrical

Transimpedance Gain (Ω):

Low Noise: 1×10^3 - 1×10^9 (adjustable in decade steps)
High Speed: 1×10^4 - 1×10^9 (adjustable in decade steps)

Noise Equivalent Power NEP ($W/Hz^{1/2}$):

5.2×10^{-14} - 1.92×10^{-10}

Bandwidth (-3 db):

200 MHz max

Hardware & Interface Connectivity

Power Requirement:

± 15 V, $+150$ mA - 100 mA, ± 200 mA

Power Supply:

Power Supply Required and Sold Separately.

USA: [#59-180](#)

Europe: [#59-180](#)

Japan: Not Available

Korea: Not Available

China: [#59-180](#)

Environmental & Durability Factors

Operating Temperature ($^{\circ}C$):

0 to $+60$

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Product Details

- Ultra-Wide Adjustable Transimpedance Gain from 10^2 to 10^{11} V/W
- Exceptional Low-Noise, High-Sensitivity Single-Beam Detection
- Optimized for Absolute Optical Power Measurements
- Designed for Direct, Alignment-Free Integration

Variable Gain Photoreceivers feature an ultra-wide adjustable transimpedance gain from 10^2 to 10^{11} V/W , enabling precise measurement of optical signals across a broad power range. Engineered for ultra-low noise performance, these photoreceivers achieve noise equivalent power (NEP) as low as 6 fW/\sqrt{Hz} , ensuring accurate detection of extremely weak optical signals. Designed for single-beam detection, they provide maximum sensitivity and dynamic range, allowing for simple, alignment-free integration into optical systems. Variable Gain Photoreceivers are ideal for applications such as photonics research, optical communication testing, and precision low-light measurements.

Note: Power supply sold separately. Please see specifications for more details.