

Mounted M62 x 0.75 Threaded - Red Filter



Stock #46-532 CLEARANCE **1 In Stock**

€51⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€51,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

AR Coating: MgF₂ **Note:**

Mounted Imaging Filter **Type:**

Hoya R-60 or equivalent **Type of Filter:**

Physical & Mechanical Properties

58.7 **Clear Aperture CA (mm):**

Outer Diameter (mm):
65.0

Substrate Thickness (mm):
2.5

Thickness with Mount (mm):
5.00

Optical Properties

Color:
Red

Cut-On Wavelength (nm):
600.00

Glass/Filter Number:
R-60

Index of Refraction (n_d):
1.53

Substrate:
Colored Glass

Surface Quality:
80-50

Wavelength Range (nm):
400 - 700

Threading & Mounting

Filter Thread:
M62 x 0.75

Mount Thickness (mm):
4.9±0.1

Mount Thickness Including Threads (mm):
7.4

Thickness of Compatible Optics (mm):
2.5

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Improve Contrast
- Isolate Spectral Regions/Colors
- Precision Colored Glass

Mounted Color Filters are ideal for machine vision and are best used with black-and-white cameras to yield increased contrast and resolution. Utilizing the principle "Like Colors Lighten Like Colors" will maximize results. Daylight Blue filters increase color temperature from 3300K to 5500K (daylight). Color camera settings (Red/Blue gain level and AWC) yield further optimization when used in conjunction with lamp selection (quartz-halogen and fluorescent). Mounted Color Filters provide wide fields of view unobtainable with angle-sensitive filters.

All filters can be threaded together via identical male and female threads on each mount. Color filters can also be used in conjunction with [mounted UV filters](#) to block unwanted ultraviolet light and protect the filters in extreme environments.

Technical Information

