

Mounted Window for 1030nm, 0.80 NA, aplanoXX Aplan Objective

See More by [AdlOptica](#)



Mounted Window

Stock **#19-495** **1 In Stock**

-

1

+

€316²¹

ADD TO CART

Volume Pricing	
Qty 1+	€316,21 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Model Number:

Window in Holder L9333.06 (+D12_515/1030)

Mounted Window

Type:

Protective window for [#19-491](#)

Note:

Physical & Mechanical Properties

8	Clear Aperture CA (mm):
29.50	Diameter (mm):
4.40	Length (mm):

Optical Properties

515, 1030	Design Wavelength DWL (nm):
510 - 545, 1020 - 1100	Wavelength Range (nm):
25 mJ @ 5ns	Damage Threshold, By Design: ☐
25 mJ @ 5ns	Damage Threshold, Pulsed:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

PRODUCT DETAILS

- Aplanatic Optical Design
- High Numerical Aperture for Small Spot Sizes
- Designs for 800 and 1030nm with Focusing Depth Up to 4mm
- [AdlOptica foXXus Multi-Focus Objectives](#) Also Available

AdlOptica aplanoXXAplan Objectives compensate for spherical aberration and coma when focusing into glass, sapphire, silicon carbide, silicon, PMMA and other transparent materials at depths up to 4mm. These objectives are designed to be used with ultrafast solid-state and fiber lasers and are optimized for 800nm (Ti:sapphire) and 1030nm (Yb:doped). Featuring C-Mount threading and an optical design insensitive to misalignment, these objectives are easy to integrate into laser systems. AdlOptica aplanoXXAplan Objectives are ideal for micromachining glass, 3D nanofabrication, waveguide recording, and selective laser etching. A collar on the objective allows for manual adjustment of focus and a replaceable front window protects from debris during materials processing.

TECHNICAL INFORMATION

