

# Mounted Window for 800nm, 0.80 NA, aplanoXX Aplan Objective

See More by [AdlOptica](#)



Mounted Window

Stock **#19-496** 1 In Stock

-

1

+

€316<sup>21</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €316,21 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

## SPECIFICATIONS

### General

**Model Number:**  
Window in Holder L9333.06 (+D12 800)

**Type:**  
Mbunted Window

|                                            |                                                       |       |
|--------------------------------------------|-------------------------------------------------------|-------|
| Protective window for <span>#19-492</span> |                                                       | Note: |
| Physical & Mechanical Properties           |                                                       |       |
| 8                                          | Clear Aperture CA (mm):                               |       |
| 29.50                                      | Diameter (mm):                                        |       |
| 4.40                                       | Length (mm):                                          |       |
| Optical Properties                         |                                                       |       |
| 800                                        | Design Wavelength DWL (nm):                           |       |
| 770 - 900                                  | Wavelength Range (nm):                                |       |
| 25 mJ @ 5ns                                | Damage Threshold, By Design: <input type="checkbox"/> |       |
| 25 mJ @ 5ns                                | Damage Threshold, Pulsed:                             |       |
| Regulatory Compliance                      |                                                       |       |
| Compliant                                  | RoHS 2015:                                            |       |
| View                                       | Certificate of Conformance:                           |       |
| Compliant                                  | Reach 250:                                            |       |

## PRODUCT DETAILS

- Aplanatic Optical Design
  - High Numerical Aperture for Small Spot Sizes
  - Designs for 800 and 1030nm with Focusing Depth Up to 4mm
  - [AdlOptica foXXus Multi-Focus Objectives](#) Also Available
- AdlOptica aplanoXXAplan Objectives compensate for spherical aberration and coma when focusing into glass, sapphire, silicon carbide, silicon, PMMA and other transparent materials at depths up to 4mm. These objectives are designed to be used with ultrafast solid-state and fiber lasers and are optimized for 800nm (Ti:sapphire) and 1030nm (Yb:doped). Featuring C-Mount threading and an optical design insensitive to misalignment, these objectives are easy to integrate into laser systems. AdlOptica aplanoXXAplan Objectives are ideal for micromachining glass, 3D nanofabrication, waveguide recording, and selective laser etching. A collar on the objective allows for manual adjustment of focus and a replaceable front window protects from debris during materials processing.

## TECHNICAL INFORMATION

