


[See all 4 Products in Family](#)

Multi-Grid Micrometer on Opal Glass w/ NIST Cert



Stock **#59-279** [CONTACT US](#)

-

1

+

€1.035^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€1.035,00 each
Qty 5+	€983,80 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Yes

NIST Certification:

Physical & Mechanical Properties

Scale Divisions:

0.5mm (25µm divisions), 1.0mm (50µm divisions),
2.0mm (100µm divisions), 4.0mm (200µm
divisions), angle grid (15° segments)

Dimensions (mm):

25.4 x 76.2	
	Thickness (mm):
1.50 ±0.100	
	Dimensional Tolerance (mm):
±0.100	

Optical Properties	
	Substrate:
Chrome on Opal Glass	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 235:
Compliant	

Product Details

- Calibrate Distortion in High Magnification Systems
- The Multi-Grid Stage Micrometer features grids of varying frequency, and is ideal for calibrating distortion in microscopic systems. Grid sizes are 0.5mm (25µm divisions), 1.0mm (50µm divisions), 2.0mm (100µm divisions) and 4.0mm (200µm divisions). Micrometer also features an angle grid (15° segments). Target is chrome on glass, 1" x 3" x 1.5mm.