

[See all 10 Products in Family](#)

## Nikon 200mm Large FOV Tube Lens

See More by [Nikon](#)



Stock **#75-379** NEW [CONTACT US](#)

- 1 +

 €1.340<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €1.340,00 each                |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

| Product Downloads                |           |
|----------------------------------|-----------|
|                                  |           |
| General                          |           |
| Type:                            | Tube Lens |
| Manufacturer:                    | Nikon     |
| Physical & Mechanical Properties |           |
| Length (mm):                     | 27.00     |
| Maximum Diameter (mm):           | 43        |
| Optical Properties               |           |
| Focal Length FL (mm):            | 200.00    |

|                       |                               |
|-----------------------|-------------------------------|
| 1x                    | Magnification:                |
| 380 - 1000            | Wavelength Range (nm):        |
| 25                    | Field Number (mm):            |
| 42                    | Entrance Pupil Diameter (mm): |
| Threading & Mounting  |                               |
| M43x0.5               | Mounting Threads:             |
| Regulatory Compliance |                               |
| <a href="#">View</a>  | Certificate of Conformance:   |

Product Details


• Superior UV Transmission

• High Numerical Aperture Designs

• Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

Technical Information



| Dimensions (mm) |               |                  |      |      |      |        |
|-----------------|---------------|------------------|------|------|------|--------|
| Stock No.       | Magnification | Parafocal Length | A    | B    | C    | D      |
| #88-374         | 4X            | 60.06            | 30.0 | 44.4 | 19.7 | M25 x0 |
| #88-375         | 10X           | 60.06            | 32.0 | 58.7 | 8.0  | M25 x0 |
| #88-376         | 20X           | 60.06            | 33.5 | 58.9 | 9.0  | M25 x0 |
| #88-377         | 40X           | 60.06            | 33.0 | 59.6 | 7.5  | M25 x0 |