

LightPath 355022 | 5.42mm Dia., 0.47 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#16-687** CLEARANCE **8 In Stock**

-

1

+

€41¹⁵

ADD TO CART

Volume Pricing	
Qty 1+	€41,15 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Compatible Window:

Thickness: 1.20 (t) (mm) Material: BK7

Lightpath Lens Code:

355022

Aspheric Lens	Type:
Collimate or Focus Laser Light	Typical Applications:
Physical & Mechanical Properties	
5.42 ±0.015	Diameter (mm):
4.2	Clear Aperture CA (mm):
2.53	Edge Thickness ET (mm):
3.27 ±0.05	Center Thickness CT (mm):
Protective as needed	Bevel:
Optical Properties	
4.47 @780nm	Effective Focal Length EFL (mm):
0.47	Numerical Aperture NA:
D-ZLaF52LA	Substrate: □
±1	Focal Length Tolerance (%):
780	Aspheric Design Wavelength (nm):
BBAR (350-700nm)	Coating:
R _{avg} ≤0.5% @ 350 - 700nm	Coating Specification:
40-20	Surface Quality:
1.06	f/#:
350 - 700	Wavelength Range (nm):
3.08	Working Distance (mm):
Infinite	Conjugate Distance:
Environmental & Durability Factors	
≤200	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

PRODUCT DETAILS

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

TECHNICAL INFORMATION

