

Olympus 20X WLI Objective

See More by [Olympus](#)



Stock #91-173 **NEW** 1 In Stock

- 1 + €6.190⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€6.190,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Model Number:
WL120XMRTC

Compatible Tube Lens Focal Length (mm):
Focal Length: 180mm

Type:
Microscope Objective

Style:
InfinityCorrected

Manufacturer:

Olympus

Note:

Designed to be used with a 180mm Tube Lens,
Sold Separately

Physical & Mechanical Properties

Field of View (mm):
1.1

Length excluding Threads (mm):
44.00

Maximum Diameter (mm):
29.8

Optical Properties

Focal Length FL (mm):
9.00

Magnification:
20X

Numerical Aperture NA:
0.60

Resolving Power (μm):
0.56

Depth of Field (μm):
0.76

Working Distance (mm):
1

Field Number (mm):
22

Parfocal Length (mm):
45

Depth of Focus (μm):
305.6

Entrance Pupil Diameter (mm):
10.80

Threading & Mounting

Mounting Threads:
RMS / 20.32mm x 36 TPI

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

Product Details

- Combines High Numerical Aperture and Broad Field of View
- Thermal Compensation & Stability Features
- Suitable for 3D Surface Metrology and Profilometry

Olympus WLI Infinity Corrected Interferometry Objectives' advanced optical design combines a high numerical aperture with a broad field of view, capturing fine surface details across large areas for visual clarity. Each objective features a built-in adjustment ring that compensates for temperature-induced focused shifts, allowing stability and consistent measurement accuracy even under unstable environmental conditions. These objectives are designed to be used with a 180mm focal length tube lens and are available in magnification of 10 – 50X. Olympus WLI Infinity Corrected Interferometry Objectives are ideal for 3D surface metrology and profilometry applications, including semiconductor inspection, precision machining, optical coating evaluation, and microelectronic characterization.