

[See all 74 Products in Family](#)

LightPath 355625 | 5.585mm Dia., 0.55 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock #16-701 **20+ In Stock**

⊖ 1 ⊕ €85⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€85,00 each
Qty 11-49	€76,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

355625 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Collimate or Focus Laser Light **Typical Applications:**

Physical & Mechanical Properties

5.59 ±0.015	Diameter (mm):
4.6	Clear Aperture CA (mm):
2.73	Edge Thickness ET (mm):
3.70 ±0.03	Center Thickness CT (mm):
Protective as needed	Bevel:

Optical Properties

4.13 @447nm	Effective Focal Length EFL (mm):
0.55	Numerical Aperture NA:
D-ZLaF52LA	Substrate: <input type="checkbox"/>
±1	Focal Length Tolerance (%):
447	Aspheric Design Wavelength (nm):
BBAR (1050-1600nm)	Coating:
R _{abs} <1.0% @ 1050 - 1600nm	Coating Specification:
40-20	Surface Quality:
0.91	f#:
40.99	Abbe Number (v_d):
1.81	Index of Refraction (n_d):
1050 - 1600	Wavelength Range (nm):
2.2	Working Distance (mm):
Infinite	Conjugate Distance:
447	Focal Length Specification Wavelength (nm):
<0.200	Transmitted Wavefront Error (λ, RMS):

Material Properties

6.9	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
-----	---

Environmental & Durability Factors

≤200	Operating Temperature (°C):
------	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

Technical Information

