

[See all 32 Products in Family](#)

# M4040, 1.1" Monochrome, Teledyne DALSA Genie Nano GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie™ Nano GigE Cameras



Stock #14-697 [CONTACT US](#)

⊖ 1 ⊕ €3.315<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€3.315,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

Monochrome **Spectrum:**

### General

Monochrome Camera **Type:**

G3-GM10-M4040 **Model Number:**

Teledyne DALSA  
Genie Nano-1GigE

**Manufacturer:**  
**Camera Series:**

## Physical & Mechanical Properties

40.6 x 29.0 x 44.0 (includes connectors and lens mount)

**Dimensions (mm):**

46

**Weight (g):**

Full

**Housing:**

## Sensor

200MB

**Image Buffer:**

1.1"

**Sensor Format:**

12.40

**Resolution (Megapixels):**

9.70

**Frame Rate (fps):**

40.00

**Frame Rate - Burst Mode (fps):**

4,112 x 3,012

**Pixels (H x V):**

3.45 x 3.45

**Pixel Size, H x V (µm):**

14.19 x 10.39

**Sensing Area, H x V (mm):**

Sony IMX253

**Imaging Sensor:**

Progressive Scan CMOS

**Type of Sensor:**

Global

**Shutter Type:**

8 bit

**Pixel Depth:**

Programmable or via external trigger

**Exposure Time:**

56.4

**Dynamic Range (dB):**

GigE Vision v1.2

**Machine Vision Standard:**

## Electrical

3.6 - 4.6 (12VDC External Power Supply)  
4.0 - 4.9 (PoE)

**Power Consumption (W):**

## Hardware & Interface Connectivity

GigE (PoE)

**Interface:**

GigE, RJ45 with Screw Locks

**Connector:**

Power over Ethernet (PoE) or via GPIO

**Power Supply:**

2 digital input, 2 digital output

**GPIOs:**

Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)

**Synchronization:**

Back Panel

**Interface Port Orientation:**

10-pin Samtec

**GPIO Connector Type:**

## Threading & Mounting

C-Mount

**Mount:**

1/4-20 with Tripod Mount Adapter [#34-966](#)

**Mounting Threads:**

## Environmental & Durability Factors

**Operating Temperature (°C):**

-20 to +60

Storage Temperature (°C):

-40 to +80

---

## Regulatory Compliance

[View](#)

Certificate of Conformance:

---

## Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne  
Authorized  
Distributor

Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.\* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

**Note:** Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

**Sapera LT** is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.